



Product data sheet

Power tools for trade & industry

EXACT ION 12-450 WK

INDUSTRIAL EXACT ION 12-450 WK



The new EXACT screwdrivers – now with lithium-ion technology!

The most important data

Torque (hard)	2 – 16 Nm
Speed	32 – 320 rpm

Part Number 0 602 494 409

Technical data

Technical data

Description	Centre grip screwdriver with angle flange
Torque, from (hard)	2 Nm
Torque, to (hard)	16 Nm
Torque (hard)	2 – 16 Nm
Torque, from (soft)	2 Nm
Torque, to (soft)	16 Nm
Torque (soft)	2 – 16 Nm
Speed, from	32 rpm
Speed, up to	320 rpm
Speed	32 – 320 rpm
Direction of rotation	R/L
Weight	1.4 kg
Comment	Values measured with 2.0 Ah battery and angle head 0 607 453 620 Below 50% speed setting eventually lower power
Bit holder	Without angle head
Drive type	Battery
Design	Centre grip
Connector type	Shut-off clutch

Noise/vibration information

Screwdriving

Vibration emission value ah	2.5 m/s ²
Uncertainty K	1.5 m/s ²

Product data sheet

Power tools for trade & industry



BOSCH
Invented for life



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

