

## Datasheet

# Single Wire Earpiece with Acoustic Tube

RS Stock number 781-1696



### Features:

- Surgical grade acoustic tube; discreet and comfortable
- Quick-fasten secure structure
- Environmental PU cable reinforced with Kevlar
- Optional ear mold allows ambient sounds
- Discreet communication in sensitive environments
- Suitable for many applications including; security personnel, hotel and catering staff, etc.



ENGLISH

## Professionally approved products. Datasheet

### Technical Specification

#### Speaker:

Dimensions: Od 19.0mm x 10.6mm

Impedance:  $73 \pm 200\Omega$  @ 1000Hz

Rated Input Power: 1mW

Rated Output Power: 300mW

Sound Pressure Level:  $117 \pm 3\text{dB}$  @1000Hz

#### Microphone:

Type: Electric Microphone

Impedance: 2.2 k Ohm

Sensitivity:  $-40 \pm 3\text{dB}$  @1000Hz

(0dB = 1V/PA)

Operating Voltage: 1.0-10VDC

#### PTT:

Dimensions: 34.9 x 14.2 x 11.8mm