

775466

Floor squeegee w/Replacement Cassette, 600 mm, Brown



Ideal for removing water and food debris from all types of flooring, this double-bladed cell rubber squeegee can be used with any Vikan handle. The cassette can be removed easily for cleaning or replacement (Series 77745 or 77749 for replacement blades).

Technical Data

| | |
|---|----------------------------------|
| Item Number | 775466 |
| Material | Polypropylene Cellular rubber |
| Complies with (EC) 1935/2004 on food contact materials¹ | No |
| FDA compliant raw material (CFR 21) | No |
| Is Halal compliant | Yes |
| Box Quantity | 10 Pcs. |
| Quantity per Pallet (80 x 120 x 200 cm) | 320 Pcs. |
| Quantity Per Layer (Pallet) | 40 Pcs. |
| Box Length | 615 mm |
| Box Width | 295 mm |
| Box Height | 210 mm |
| Length/Depth | 600 mm |
| Width | 85 mm |
| Height | 115 mm |
| Gross Weight | 0,33 kg |
| Net Weight | 0,29 kg |
| Cubik metre | 0,0059 M3 |
| Max. cleaning temperature (Dishwasher) | 80 °C |
| Max usage temperature (non food contact) | 80 °C |
| Min. usage temperature³ | -20 °C |
| Min. pH-value in usage concentration | 2 pH |
| Max. pH-value in Usage Concentration | 10,5 pH |
| GTIN-13 Number | 5705022014954 |
| GTIN-14 Number (Box quantity) | 15705028014986 |
| Commodity Code | 96039099 |
| Country of origin | Denmark |

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

3. Do not store the product below 0° Celsius.