

Optimal Performance in rugged conditions

BMP41 Label Printer



Want added durability in an industrial design? Get the **BMP41 Label Printer**. Reliable for your most detailed work and rugged enough to use every day, it's a must-have for datacom and electrical professionals.

Create and print labels on-the-spot with its QWERTY keypad, or in batches at the office with Brady Workstation software. This printer can help you power through work faster with its programmed pre-set label options for wire marking, flagging and patch panel ID. The BMP41 is ready for it all, every day. It's that dependable.

Speed — Prints 33mm/second at 300 dpi


Durability — Features rubber grips, a long-life rechargeable NiMH battery and withstands 1.2 m drops

Flexibility — Prints labels up to 25 mm wide (continuous and pre-sized) from a cartridge

Convenience — Window on printer lets you view 100+ different installed cartridges

Printer part numbers

Article No.	Order Reference	Description
133254	BMP41-KIT-EU	BMP41 Label Printer - EU
198648	BMP41-EU-PWID	BMP41 Label Printer - EU with Brady Workstation PWID Suite
711213	BMP41-KIT-UK	BMP41 Label Printer - UK
198629	BMP41-UK-PWID	BMP41 Label Printer - UK with Brady Workstation PWID Suite

 The Basic Suite is included with every printer, all you need to do is download it. Workstation.BradyID.com/Free

 Quickly identify your products and wires with customised text or graphical labels, using serialised or imported data. Workstation.BradyID.com/ProductandWire



Printer technical data

Specifications	
Print Technology	Thermal Transfer
Print Resolution (dpi)	300 dpi
Print Speed (mm/sec)	33.00 mm/s
Colour Capability	Monocolour
Continuous vs Die-cut Labels	Continuous and Die-cut
Max. Label Width (mm)	25.40 mm
Max. Print Length	7620.00 mm
Recommended Usage per Day	250
Stand-alone Printing (Detached from PC)	Stand-alone & Peripheral
Connectivity Options	USB
PC Connectivity	Yes
Bar Code Type	Code 39 and 128, other via software
Built-in Symbols	480
Software Compatibility	Brady Workstation CodeSoft
Physical Properties	
Size - W x H x D (mm)	152.40 x 292.00 x 89.00
Weight (kg)	1.29 kg
Keyboard Type	QWERTY
Display	LCD
Cutter	Single Hand Manual Actuate Straight Cut
Warranty	2 years



Easily store your portable printer, some consumables and a number of accessories in a lightweight soft bag with protective padding that keeps your identification tools neatly together.

Electrical kit

Article No.	Order Reference	Description
198650	BMP41-EU-ELEC	BMP41 Label Printer - Electrical Kit - EU
198652	BMP41-UK-ELEC	BMP41 Label Printer - Electrical Kit - UK

Kit includes one of each

BMP41 Label Printer - EU or BMP41 Label Printer - UK	
BMP41-HC	BMP41 Hard Case
BMP41-MAGNET	BMP41 Magnet
BWS PWID Suite	Brady Workstation PWID Suite
M-91-427	Black on White/Transparent Self-laminating Vinyl, 25.40 mm x 38.10 mm, 180 labels / Cartridge
MC1-1000-595-WT-BK	Black on White Vinyl, 25.40 mm x 7.62 m, 1 / Cartridge
M-131-499	Black on White Nylon Cloth, 12.70 mm x 25.40 mm 180 labels / Cartridge

Voice & datacom kit

Article No.	Order Reference	Description
198649	BMP41-EU-DATA	BMP41 Label Printer - Voice & Datacom Kit - EU
198651	BMP41-UK-DATA	BMP41 Label Printer - Voice & Datacom Kit - UK

Kit includes one of each

BMP41 Label Printer - EU or BMP41 Label Printer - UK	
BMP41-HC	BMP41 Hard Case
BMP41-MAGNET	BMP41 Magnet
BWS PWID Suite	Brady Workstation PWID Suite
M-48-427	Black on White/Transparent Self-laminating Vinyl, 25.40 mm x 19.05 mm, 200 labels / Cartridge
MC1-1000-595-WT-BK	Black on White Vinyl, 25.40 mm x 7.62 m, 1 / Cartridge
MC-375-422	Black on White Polyester, 9.53 mm x 7.62 m, 1 / Cartridge

BMP41 Accessories

Article No.	Order Reference	Description
114883	M-AC-143110	AC Adaptor, USA 120V
133255	BMP41-BATT	Rechargeable Nickel Metalhydride battery for the BMP41 and BMP61 printers
133257	BMP41-HC	BMP41 Hard Case
134176	BMP41-MAGNET	BMP41 Magnet
143114	USB-CABLE	BMP41-BMP50 Series USB Cable
150618	BMP-SC-2	Protective softbag for portable printers - BMP41/BMP61
710612	M50-71-AC-BC-EU	AC Adaptor, Europe 220V
710613	M50-71-AC-BC-UK	AC Adaptor, UK 240V
711222	BMP41-QC-EU	EU External Battery Quick Charger for BMP41 and BMP61
711223	BMP41-QC-UK	UK External Battery Quick Charger for BMP41 and BMP61

10/02/2021

EUR-M-428-EN

© 2021 Brady Worldwide, Inc. All Rights Reserved.

