


ISSUE: ABJULVOL1

## Trade LED flush bulkhead





MLA part code	BT14	BT14D
Description	TRADE LED FLUSH + SENSOR	
Net weight (kg)	.74	
Wattage (W)	14	
Lumens (lm)	910 ± 5%	1030 ± 5%
Efficacy (lm/W)	65	73
Overall dimensions	Diameter – 315mm	
	Projection – 74mm	
CCT	4000K	6000K
LED Colours	Cool white	Daylight
Input voltage	Mains 230V 50Hz	
Construction	Polycarbonate	
Finish	White	
Diffuser	Opal	
Sensor type	Microwave	
Class	Class II double insulated	
IP rating	IP44	
Warranty	3 Years	
Lamp replacement	Yes (BT14DL)	
available	·	
Photometric data	Yes	
Dimmable	No	
Origin of Manufacture	China	
Quality assurance system	IS09001	
Declaration of Conformity	Yes	
(held on file)	162	
Manufactured &	BS EN 60598	
accordance with		
EAN	5055559197348	5055832937661



