

FiberTuf™

76501

light mechanical protection and good grip for dry applications.



Multi Purpose



Light Duty

- Made from aromatic polyester fibre, the Ansell FiberTuf 76-501 Light Mechanical Work Gloves are ideal for providing hand protection when performing dry applications that require light mechanical protection.
- They feature PVC dots on the palm side for improved gripping, and are available in a range of sizes to ensure the most comfortable and secure fit.
- Offers higher performance and durability than traditional cotton and polyamide gloves.



Industries

- Construction
- Transportation
- Automotive
- Machinery and Equipment
- Logistics
- Metal fabrication

Applications

- Inspection (picking, checking and marking)
- Packaging
- Light assembly tasks
- General handling
- Assembly of parts
- Assembly of white goods

FiberTuf™

76501

light mechanical protection and good grip for dry applications.

Key Features

- Aromatic polyester fibre for optimal results in dry applications requiring light mechanical protection
- PVC dots on palm side improve gripping for easier and safer handling
- Washable at 40°C for ongoing hygiene maintenance
- Knitwrist cuff provides easier donning
- Available in a range of sizes for a comfortable fit
- Suitable for a range of applications, from automotive and construction to packaging and general handling
- Can be used either as primary glove or as underglove to protect against cold wherever required

Performance Standards & Regulatory Compliance

REACH Compliant



214XA

Specifications

FiberTuf 76-501	Finishing: Dotted on Palm Side Coating Material: PVC Liner Material: Synthetic fiber, Polyester Cuff Style: Knitwrist	13	7, 8, 9, 10	240-270mm	Blue	• 12 pairs/bag, 12 bags/carton
-----------------	--	----	-------------	-----------	------	--------------------------------

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2022 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

