



FOAM MODULE 1/3 10 BITS DYNA 14X18 INCH FORK **DFC-J10PMM**

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 08:53:33





DESCRIPTION

FOAM MODULE 1/3 10 BITS DYNA 14X18 INCH FORK

Foam module with 10 torque wrench bits (DFC-...) ideal for all industrial applications. The ten 14x18 torque wrench bits with forks in inches guarantee precise tightening. Bits in inches with satin finish. Forged Chrome Vanadium steel. Can be used with all SAM torque wrench models with 14x18 mm rectangular attachment. Conform to standard ASME B107.100. The bits are stored in a made-to-measure foam tray.

SPECIFIC DATA

| | |
|-----------------|--|
| Designation | FOAM MODULE 1/3 10 BITS DYNA 14X18 INCH FORK |
| Sales reference | DFC-J10PMM |
| Weight (kg) | 1.775 |

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â,-

<https://www.sam-outillage.com/>



| | |
|-------------|-------------------------|
| Width (mm) | 180 |
| Length (mm) | 410 |
| Height (mm) | 40 |
| Guarantee | O SAM TOOL guarantee. |

Guarantee applied

O | SAM TOOL guarantee.

Guarantee without time limit on the tools used under normal conditions.

>> [Find out more](#)

Toolset



x 10

OFFSET OPEN END , RECTANGULAR ATTACHMENT 14x18mm

DFC-...-pouce

Ref : 1 - 1"1/4 - 1/2 - 11/16 - 13/16 - 15/16 - 3/4 - 5/8 - 7/8 - 9/16



x 1

EMPTY 1/3 FOAM MODULE FOR COMPOSITION DFC-J10PMM

MODM-139

Ref : MODM-139

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

