

DOUBLE EAR O CLIPS IN BAG

Standard treated steel o clips



Part number	Ø min/max (mm)	Net weight (Kg)	Pack.
709P	7.00 / 9.00	0,015	1
911P	9.00 / 11.00	0,02	1
1113P	11.00 / 13.00	0,025	1
1315P	13.00 / 15.00	0,032	1
1517P	14.00 / 17.00	0,039	1
1518P	15.00 / 18.00	0,00393	1
1720P	17.00 / 20.00	0,00441	1
1821P	18.00 / 21.00	0,00485	1
2023P	20.00 / 23.00	0,00351	1
2225P	22.00 / 25.00	0,0031	1
2327P	23.00 / 27.00	0,00397	1