




FEMALE END VIEW




SPECIFICATIONS


CONTACT CARRIER MATERIAL	NYLON OR TPU
CONTACT MATERIAL/PLATING	BRASS/GOLD
RATED CURRENT [A]	4.0 A
RATED VOLTAGE [V]	250 V
HOUSING MATERIAL/PLATING	BRASS/NICKEL
CONDUCTORS	PCB PINS
TEMPERATURE RATING	-30°C to +80°C (-22°F to +176°F)
PROTECTION CLASS	MEETS NEMA 1,3,4,6P AND IEC IP68



BOARD LAYOUT  
SCALE 2:1



RIGHT ANGLE  
CONNECTOR ORIENTATION



DIMENSIONAL VIEW

NOTES:

- FOR OTHER RIGHT ANGLE CONNECTOR ORIENTATIONS, ROTATE BOARD LAYOUT TO DESIRED ORIENTATION OR ROTATE 5-HOLE PINOUT IN INCREMENTS OF 60°.

<p>RELATED DOCUMENTS</p> <ol style="list-style-type: none"> <li>INSERT SHEET 10240100</li> <li></li> <li></li> <li></li> </ol>		<p>3RD ANGLE PROJECTION</p>		<p>THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.</p>		<p>3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com</p>	
<p>MATERIAL SEE SPECIFICATIONS</p>		<p>DRFT IK DATE 10/21/97</p> <p>APVD SCALE 2=1.0</p>		<p>DESCRIPTION FK 4.5-PCB</p>			
<p>FINISH SEE SPECIFICATIONS</p>		<p>UNIT OF MEASUREMENT <b>MILLIMETER [ INCH ]</b></p>		<p>IDENTIFICATION NO. U1117-44</p>		<p>REV H</p>	
<p>H UPDATE CLOSE-UP DETAIL OF PINS RDS 11/27/13 44144</p>		<p>DO NOT SCALE THIS DRAWING</p>		<p>FILE: U1117-44</p>		<p>SHEET 1 OF 1</p>	
<p>REV DESCRIPTION BY DATE ECO NO.</p>							