Product data sheet
Characteristics

A9L40501
iPRD40r modular surge arrester - 1P + N - 350V - with remote transfert

Main

Range of product	Acti 9
Product name	Acti 9 iPRD
Product or component type	Surge arrester with pluggable cartridge
Device short name	IPRD40r
Device application	Distribution
Poles description	1P + N
Remote signalling	With
Signal contacts composition	1 SD (1 C/O)
Surge arrester type	Electrical distribution network
Earthing system	TT TN-S

Complementary

Surge arrester class type	Type 2
Surge arrester technology	MOV + GDT
[Ue] rated operational voltage	230/400 V AC (+/- 10 %) at 50/60 Hz
[In] nominal discharge current	Common mode: 15 kA (L/PE) Common mode: 15 kA (N/PE) Differential mode: 15 kA (L/N)
[Imax] maximum discharge current	Common mode: 40 kA L/PE Common mode: 40 kA N/PE Differential mode: 40 kA L/N
[Uc] maximum continuous operating voltage	Common mode: 260 V N/PE Differential mode: 350 V L/N
Maximum [Up] voltage protection level	Common mode <1.4 kV type 2 N/PE Differential mode <1.6 kV type 2 L/N
[Ut] temporary overvoltage	337 V L/N 5 s withstand 1200 V N/PE 200 ms safe failure mode 442 V L/PE 5 s withstand 1455 V L/PE 200 ms safe failure mode
Disconnector device type	Associated circuit breaker iC60H 50 A curve C - Icu 15 kA Associated circuit breaker iC60N 40 A curve C - Icu 10 kA Associated circuit breaker NG125H 63 A curve C - Icu 36 kA Associated circuit breaker NG125L 63 A curve C - Icu 50 kA Associated circuit breaker NG125N 40 A curve C - Icu 25 kA Associated fuse gG 63 A - Icu 15 kA Associated fuse gG 80 A - Icu 50 kA
[Isccr] short-circuit current rating	50 kA
Signalling circuit voltage	0.25 A/250 V AC 50/60 Hz
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	4
Height	85 mm
Width	36 mm
Depth	69 mm
Net weight	220 g
Colour	White (RAL 9003)
Response time	<= 25 ns
[Ipe] Ground residual current	0.003 MA 0.6 mA

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Connections - terminals	Tunnel type terminal (top or bottom) 4…16 mm² flexible Tunnel type terminal (top or bottom) 4…16 mm² flexible with ferrule Tunnel type terminal (top or bottom) 2.5…25 mm² flexible
Wire stripping length	14 mm
Tightening torque	3.5 N.m

Environment

Standards	EN 61643-11:2012 IEC 61643-11:2011
Product certifications	CE
Quality labels	NF KEMA-KEUR
IP degree of protection	IP40 on front face: conforming to IEC 60529 IP20 built-in: conforming to IEC 60529
IK degree of protection	IK03 conforming to IEC 62262
Relative humidity	5…95 %
Operating altitude	2000 m
Ambient air temperature for operation	-25…60 °C
Ambient air temperature for storage	-40…85 °C

Packing Units

Package 1 Weight	0.248 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACh Regulation	REACh Declaration
REACh free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months