

Versatile Compact Foot Switch

RS Stock No. 116-877



Degree of protection	IP20
Materials of Construction	Pressed steel cover & base.
Colour	Black
Cable Connection	Provided with an adjustable strain relief clamp that accommodates a wide variety of cable sizes.
Contact Action	Momentary SPDT
Electrical Rating	10A 125-250V a.c., 0.375kW 125-250V a.c.
Features & Benefits	Compact in size and light weight. Nonskid base pads. Internal fixing for securing to floor or equipment.
Weight	0.2kg
Size	(See below)

