



HL-5R - SENSOR HEADTORCH



RUBBERISED HEAD BRACKET



325
LUMEN



2-5¹/₂H
RUNTIME



38M
RANGE



IP65/IK07
IP RATING

- 325 Lumen white COB LED
- Sensor mode for hands-free operation
- 60° Rotational head
- Fully adjustable non-slip silicone headband included
- IP65 dust & water resistant
- IK07 Shock resistant
- Red-to-Green charging indicator light

- Quick 1A micro-USB rechargeable - 2 ½ hours charge time
- 1m micro-USB charging cable included

BATTERY 3.7v 1500 mAh Li-Polymer Rechargeable Battery

WEIGHT 110g

DIMENSION Headtorch: 48 x 79 x 46mm