



EU regulation 2016/425 attest n°0075/057/162/10/19/3148 delivered by CTC, notified body n°0075

BLACKWELDER

WELDING GLOVES



 EN 388	EN388:2016
Resistance to abrasion: Blade cut resistance: Tear resistance: Puncture resistance: Blade cut resistance according to ISO13997 :	Levels : ●●●○ ●●●● ●●●○ ●●●○ D
 EN 407	EN407
Burning behaviour: Contact heat: Convective heat: Radiant heat: Small splashes of molten metal: Large splashes of molten metal:	Levels : ●●●● ●○○○ ●●●○ ●○○○ ●●●● X
Sizes	Packaging
7 - 8 - 9 - 10 - 11 - 12	10 per packet / 60 per box

PPE Category II

Welding glove with palm in waterproof brown split leather, back in waterproof black grain leather. Lined with 100% para-aramid thread and mineral filament. Elastic tightening on the back. 15 cm cuff in waterproof black split leather. 100% para-aramid sewing thread.

THE + PRODUCT

- SOFTNESS**
- RESISTANCE**
- COMFORT**

RELEVANT SECTORS

- Automotive manufacturing and supply industry
- Assembly works
- Metal manufacturing and processing industry
- Welding works
- Engineering industry and industrial maintenance
- Building and public works



LEBON International S.à.r.l
 Immeuble Laccolith
 20, rue Eugène Ruppert L-2453 Luxembourg
 Website : www.lebonprotection.com
 TEL : +352 26 49 36 07
 FAX : +352 26 49 35 35