



Swivel Castor, 35mm PU, ball bearing, 100kg

Heavy-load and small PU castor

PRODUCT

Article number	EP2BA035-23B	EP2OA035-23B
		

Product Details

Castor assembly : Pressed steel, plate or central bolt-hole fitting, zinc-plated protection.

Swivel : Swivel on two rows of balls

Rim : machined steel.

Tread : Cast bonded polyurethane. Non-marking.

Hub : symmetrical with shielded ball bearing.

Specifications	Plate	Bolt Hole
Wheel Diameter - ØD ± 1%	35 mm	35 mm
Hub Type	Ball bearing	Ball bearing
Hub Length	25 mm ±1	25 mm ±1
Width of Tread	25mm ±1	25 mm ±1
Width of Tread-on floor	25 mm ±1	25 mm ±1
Overall Height	58 mm	58 mm
Offset	20 mm	20 mm
Fixing Plate Dimensions	60x60 mm	-
Fixing Centres	48/38 x 48/38 mm	-
Fixing Hole Size	6,3 mm	11 mm
Hardness of tread A ±3	A 93° Shore	A 93° Shore
Load capacity	100 Kg	100 Kg
Temperature	-5 / +50 °C	-5 / +50 °C

TECHNICAL DATA

Applications :

High load capacity. Low bulk.

Low starting effort.

Abrasion resistant.