

Univers	Professional
Type	Lighting
Category	Headlamps
Subcategory	Rechargeable Batteries



R1

The R1 rechargeable battery, 3200 mAh (3,7 V / 11,84 Wh), provides excellent lighting performance for the XENA® headlamp, even at low temperatures. It recharges with a USB-C port and has a five-level gauge for precise monitoring of the battery charge level. It is equipped with red lighting for visibility from behind and can be used to charge other electronic devices.



Red lighting, continuous or strobe, can be used to signal your location.



A separate button allows the red lighting to be turned on or off directly. It also displays the five-level gauge for precise monitoring of the battery charge level.



Simple charging with a USB-C port. It can be used as a spare battery to charge electronic devices.

Short Description Rechargeable battery for XENA® headlamp. 3200 mAh

Selling Points

- Easy charging via USB-C port
- Five-level gauge for precise monitoring of the battery charge level
- Red lighting, continuous or strobe, to remain visible from behind at night and a separate button to quickly turn it on or off
- Can be used to charge other electronic devices
- Performs well at low temperatures

Specification

- Weight: 80g
- Certification(s): CE, UKCA
- Type: Batterie rechargeable Lithium-Ion 3200 mAh (3,7 V / 11,84 Wh)
- Charging time: 3.5 h
- Number of charging cycles: 300
- Watertightness: IP67 (waterproof in up to 1 meter of water for 30 minutes)
- Fall resistance: 1 meter (ANSI/PLATO FL 1)

Lighting Performance

Lighting Color	Lighting Levels	Brightness	Distance	Burn Time
Red	Continuous	1 lm	1 m	75 h
	Strobe	Visible at 200 m for 250 h		

Specifications by reference

Reference(s)	E037AA00
Made in	CN
Guarantee	2 years or 300 charging cycles
Inner Pack Count	1
Quantity Per Box	100
EAN	3342540838222

Accessory(ies) R1 Extension Cord

Related product(s) XENA®