

Product selected: LS100 T16 8W cabinet Lite - satin silver

Shallow cross section 23mm x 70mm. Satin silver finish. Ribbed diffuser for even light distribution. Main cables and connector Included. High frequency ballast. 8W to 35W T5 Sylvania 830 lamps supplied

Product Image



Product Line Drawing



DIMENSIONS (MM)

Lamp	L	I	H
8W	350	23	70
13W	575	23	70
14W	610	23	70
21W	910	23	70
28W	1210	23	70
35W	1510	23	70

Lamp(s)



Certifications



Product Details

Order code	2426014
Item name	LS100 T16 8W cabinet Lite - satin silver
Mounting	Ceiling surface
Place of use	Interior
Colour	White
Length (mm)	350
Width (mm)	23
Height (mm)	70
Housing	Extruded Aluminium
Distribution type	Symmetric
Diffuser finish	Ribbed
Lamps description	1 x 8W T16 G5
Lamp included	Yes
Number of heads	1
Control gear availability	Included
Control gear type	Electronic
Control gear mounting	Integral
Voltage (V)	230