

7ML5610-0BD20



Image similar

Pointek CLS100 RF Capacitance point level switch, PPS process connection. Detects level and interface in liquids, solids, slurries, and foam. Compact, with 100 mm (4 inch) insertion, adaptable sensitivity, with the ability to tune out build-up on probe. . Process connection: R 1" ((BSPT), EN 10226/PT (JIS-T), JIS B 0203) (PPS probe body) Approvals: General Purpose (CSA, FM) Versions/Options: Enclosure version, PPS process connection, M20x1.5 Overfill Protection: Not Required

List Price	Show prices
Customer Price	Show prices
Additional Services	For this product we can offer Services like Spare Part Delivery/Repair/Exchange. You have currently no rights to enter the Service Web Shop for that. For further information & to order this service, please contact your local Spares&Repair Partner For this product we can offer extended warranty contracts EEO (material exchange for a single product) OEM RSC (Repair Service Contract for a whole machine) For further information & to order these services, please contact your local Siemens Service Partner
Service & Support (Manuals, Certificates, FAQs...)	Download

Services (14)



9LF1110-6DA11-1AA1

The service "Service Card Priority" for technical expert consulting by phone contains 1 case. A case...



9LF1110-6DA11-5AA1

The service "Service Card Priority" for technical expert consulting by phone contains 5 cases. A case...



9LF1110-6DA11-1BA1

The service "Service Card Priority" for technical expert consulting by phone contains 10 cases. A cas...



9LF1110-6DA12-1AA1

The service "Service Card Premium" for technical expert consulting by phone contains 1 case. A case...

Show all

Product

Article Number (Market Facing Number)	7ML5610-0BD20
Product Description	Pointek CLS100 RF Capacitance point level switch, PPS process connection. Detects level and interface in liquids, solids, slurries, and foam. Compact, with 100 mm (4 inch) insertion, adaptable sensitivity, with the ability to tune out build-up on probe. . Process connection: R 1" ((BSPT), EN 10226/PT (JIS-T), JIS B 0203) (PPS probe body) Approvals: General Purpose (CSA, FM) Versions/Options: Enclosure version, PPS process connection, M20x1.5 Overfill Protection: Not Required
Product family	Not available
Product Lifecycle (PLM)	PM300:Active Product

Price data

Price Group / Headquarter Price Group	8L3
List Price	Show prices
Customer Price	Show prices
Metal Factor	None

Delivery information

Export Control Regulations	ECCN : EAR99 / AL : N
Standard lead time ex-works	1 Day/Days
Net Weight (kg)	0.400 Kg
Package size unit of measure	Not available
Quantity Unit	1 Piece
Packaging Quantity	1

Additional Product Information

EAN	Not available
UPC	Not available
Commodity Code	90261029
LKZ_FDB/ CatalogID	F101-4
Product Group	4717
Group Code	R3P5
Country of origin	Malta
Compliance with the substance restrictions according to RoHS directive	Since: 20/07/17
Product class	C: products manufactured / produced to order, which cannot be reused or re-utilised or be returned against credit.
WEEE (2012/19/EU) Take-Back Obligation	Yes
REACH Art. 33 Duty to inform according to the current list of candidates	

Classifications

	Version	Classification
eClass	6	27-20-05-03
eClass	7.1	27-20-05-03
eClass	8	27-20-05-03
eClass	9	27-20-05-03
eClass	9.1	27-20-05-03
