

BC 107,6-KIT-RPI-7035+PCB - Housing set



1311017

<https://www.phoenixcontact.com/in/products/1311017>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Empty enclosure, DIN rail mounting, light gray (7035), for Raspberry Pi computer (suitable for Raspberry Pi A+, B+, B2, B3, B4), incl. perfboard and holder, for connection to HBUS and GPIO strip, width: 107.6 mm, height: 89.7 mm, depth: 60.7 mm

Your advantages

- Tool-free mounting
- Plenty of space for additional circuits on matrix or additional boards
- GPIO strip can be used with PTSM series connection technology
- Easy module-to-module connection, thanks to bus connection via DIN rails

Commercial data

Item number	1311017
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	*****
Product key	ACHBAE
GTIN	4063151603090
Weight per piece (including packing)	210.622 g
Weight per piece (excluding packing)	158.5 g
Customs tariff number	85366990
Country of origin	DE

BC 107,6-KIT-RPI-7035+PCB - Housing set



1311017


<https://www.phoenixcontact.com/in/products/1311017>

Technical data

Product properties

Product type	Stackable housing set
Housing type	DIN rail housing for use in distribution boards in accordance with DIN 43880
Housing series	BC
Type	Housing set
Ventilation openings present	yes

Dimensions

Dimensional drawing	
Width	107.6 mm
Height	89.7 mm
Depth	60.7 mm
Depth from top edge of DIN rail	54.7 mm

Material specifications

Color (Upper housing part)	light gray (RAL 7035)
Color (Lower housing part)	light gray (RAL 7035)
Flammability rating according to UL 94	V0
Insulating material	Polycarbonat
Housing material	PC

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Relative humidity (storage/transport)	95 %

PCB data

Type of PCB mount	Latching
-------------------	----------

Mounting

BC 107,6-KIT-RPI-7035+PCB - Housing set



1311017

<https://www.phoenixcontact.com/in/products/1311017>

Mounting type	DIN rail mounting/panel mounting
---------------	----------------------------------

Packaging specifications

Type of packaging	packed in cardboard
Outer packaging type	Carton

BC 107,6-KIT-RPI-7035+PCB - Housing set

1311017

<https://www.phoenixcontact.com/in/products/1311017>



Drawings

Dimensional drawing



Schematic figure for illustrating the item dimensions. The figure is not of the desired product. For further details, refer to the product drawings in the "Downloads" tab.

BC 107,6-KIT-RPI-7035+PCB - Housing set



1311017

<https://www.phoenixcontact.com/in/products/1311017>

Classifications

ECLASS

ECLASS-11.0	27182702
ECLASS-13.0	27190301

ETIM

ETIM 9.0	EC001031
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

BC 107,6-KIT-RPI-7035+PCB - Housing set



1311017

<https://www.phoenixcontact.com/in/products/1311017>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in