

**ZM115** **Precision locknut**

Precision locknut ZM, accessory ZM..

**Technical information****Main Dimensions & Performance Data**

|                 |                         |                           |
|-----------------|-------------------------|---------------------------|
| d               | M115X2                  | Thread                    |
| D               | 150 mm                  | Outside diameter          |
| h               | 22 mm                   | Height                    |
| M <sub>A</sub>  | 20 Nm                   | Mounting torque set screw |
| F <sub>aB</sub> | 550,000 N               | Breaking load, axial      |
| M <sub>L</sub>  | 550 Nm                  | Breakawag                 |
| M <sub>AL</sub> | 400 Nm                  | Mounting torque reference |
| M <sub>M</sub>  | 56.2 kg*cm <sup>2</sup> | Mass moment of inertia    |
| ≈m              | 1.204 kg                | Weight                    |

**Dimensions**

|                |        |                         |
|----------------|--------|-------------------------|
| d <sub>1</sub> | 137 mm | Plant diameter outside  |
| t              | 5 mm   | Hight retaining slot    |
| b              | 12 mm  | Width retaining slot    |
| c              | 11 mm  | Distance bore           |
| m              | M10    | Threaded - threaded pin |