



**fitted with**

- work equipment**
- connected load**
- power consumption**
- light distribution**
- Beam Angle**
- light colour**
- color rendering index (CRI)**
- system of protection**
- class of protection**
- usage**
- luminaire body**
- lamp cover**
- weight (net)**
- mains lead**
- fastening**
- special features**

**LED**

- Energy efficiency category A+
- without ballast
- depends on the ballast
- approx. 3 W
- direct, narrow-angled beam
- 6°
- daylight white, approx. 5600 K
- > 75
- IP 67
- III
- external
- aluminium, anodised, Jet black
- glass screen
- approx. 0.3 kg
- approx. 1.5 m; with free stranded wires
- threaded hole 1;5xM18
- pivoting through ball joint, Spot with 6° angle of reflected beam

**illuminance**

Comment: 700mA  
Distance: 50 cm

Em: 1219 lx  
Emax: 8966 lx  
Emin: 69 lx

