



## 2690Z0

### Headlamp

#### HeadsUp Lite™

Regardless of the job, the 2690Z0 HeadsUp Lite™ won't leave you in the dark. With 74 lumens of LED light, 11 hours of battery run time and weighing in at 116 gr (4.1 ounces), it's brighter, more efficient, compact and lighter than other headlamps in its class. The no-nonsense rotary bezel switch is easy to operate, even when wearing bulky gloves.

The 2690Z0 is made of impact and chemical resistant Anti-static Impact Modified PC/PBT and it's water resistant for all-weather use. It comes with an adjustable and comfortable cloth strap, as well as a heavy duty rubber strap that will not slip off your helmet.

Being certified to ATEX safe for use in high-risk hazardous locations, Zone 0 (Category 1) areas, the penlight 2690Z0 HeadsUp Lite is ideal for professionals who work in chemical, pharmaceutical, power, oil and gas, and fire rescue industries. Get the 2690Z0 HeadsUp Lite™ from Peli.

Regardless of the job, the 2690Z0 HeadsUp Lite™ won't leave you in the dark. With 74 lumens of LED light, 11 hours of battery run time and weighing in at 116 gr (4.1 ounces), it's brighter, more efficient, compact and lighter than other headlamps in its class. The no-nonsense rotary bezel switch is easy to operate, even when wearing bulky gloves.

The 2690Z0 is made of impact and chemical resistant Anti-static Impact Modified PC/PBT and it's water resistant for all-weather use. It comes with an adjustable and comfortable cloth strap, as well as a heavy duty rubber strap that will not slip off your helmet.

Being certified to ATEX safe for use in high-risk hazardous locations, Zone 0 (Category 1) areas, the penlight 2690Z0 HeadsUp Lite is ideal for professionals who work in chemical, pharmaceutical, power, oil and gas, and fire rescue industries. Get the 2690Z0 HeadsUp Lite™ from Peli.



## CONFIGURATIONS

**2690Z0** - Standard

## DIMENSIONS

**Length:** 2.81"

## MATERIALS

**Body:** Anti-static Impact Modified PC/PBT

**O-Ring:** EPDM

**Lens:** Polycarbonate (PC)

**Shroud:** Anti-static Impact Modified PC/PBT

**Contact Spring Retainer:** Nickel-Plated Phosphore Bronze

## COLOURS








Black

## LIGHT SPECS

**Lamp Type:** LED

**Lamp Life:** 10000 hrs

FL1 STANDARD	HIGH
	74 LUMENS
	11h 0mins
	92m
	2124cd
	IPX7

## POWER

**Battery Size:** AAA

**Battery Type:** Alkaline  
**Battery Quantity:** 3  
**Batteries Included:** yes  
**Volts:** 4.5v

## WEIGHT

**Weight With Batteries:** 4.1 oz  
**Weight Without Batteries:** 2.8 oz

## SWITCH

**Switch Type:** One-handed Rotary Switch  
**Light Modes:** On / Off

## CERTIFICATIONS

ATEX Zone 0

## OTHER

**Minimum Pack:** 1  
**Package Code:** C

**Peli Products, S.L.U.**

c/ Provença, 388, Planta 7 • Barcelona, Spain 08025 • Phone: +34 934 674 999  
[info@peli.com](mailto:info@peli.com) • [www.peli.com](http://www.peli.com)