

IS-3 Standard ; 0 ... 16 bar; 4...20 mA, 2-wire

IS-3 Standard ; 0 ... 16 bar; 4...20 mA, 2-wire

Item number:	14122697
Quantity:	1 pcs.
Order code:	IS-3-0-2211-1ZZ-BBKHSZZ-GTA3ZZZ-UAZZ 6W101AIS3ZZSF2ASQOGSI3
Overview:	IS-3 Standard ; 0 ... 16 bar; 4...20 mA, 2-wire @ 10 ... 30 V DC Accuracy: 0.5% of span G 1/2 B EN 837 Sealing: without Wetted parts: stainless steel Adjustability: Zero/span adjustable angular connector acc. to DIN EN 175301-803 A PG9 Cable material: without Cable length: without U+=1, U-=2 permitted media temperature: -20...+80°C Approvals: ATEX/IECEX II 1/2G Ex ia IIC T4/T5/T6 Ga/Gb, I M1 Ex ia I Ma Additional certifications: without Special features: without Test protocol: without test protocol Additional ordering information: without Specifications according to data sheet: PE 81.58
Details:	IS-3 Standard ; 0 ... 16 bar; 4...20 mA, 2-wire @ 10 ... 30 V DC Accuracy: 0.5% of span G 1/2 B EN 837 Sealing: without Wetted parts: stainless steel Adjustability: Zero/span adjustable angular connector acc. to DIN EN 175301-803 A PG9 Cable material: without Cable length: without U+=1, U-=2 permitted media temperature: -20...+80°C Approvals: ATEX/IECEX II 1/2G Ex ia IIC T4/T5/T6 Ga/Gb, I M1 Ex ia I Ma Additional certifications: without Special features: without Test protocol: without test protocol Additional ordering information: without

Date: 23/01/2024



Specifications according to data sheet: PE 81.58