
non-return valve HA-M5-QS-4 Part number: 153444

FESTO





Data sheet

Feature	Value
Valve function	Non-return function
Pneumatic connection, port 1	M5
Pneumatic connection, port 2	QS-4
Mounting type	Threaded
Standard nominal flow rate	148 l/min
Operating pressure	-1 10 bar
Ambient temperature	0 60 °C
Material housing	Nickel-plated brass
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Min. differential pressure, opening	0.1 bar
Min. differential pressure, closing	0.2 bar
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further
	operation)
Product weight	7.2 g
Materials note	Conforms to RoHS