



## 3616 - EQUAL BULKHEAD CONNECTOR



<b>maximum working pressure</b>	30 bar 3 MPa 435 psi
<b>working temperature</b>	-25 to 150 °C -13 to 302 °F 248 to 423 °K
<b>vacuum capability</b>	755 mm Hg
<b>body</b>	FDA CHEMICAL NICKEL PLATED BRASS
<b>retaining nut</b>	FDA CHEMICAL NICKEL PLATED BRASS
<b>'O'-rings</b>	FKM
<b>collar</b>	FDA CHEMICAL NICKEL PLATED BRASS
<b>sealing washer</b>	FDA CHEMICAL NICKEL PLATED BRASS





Part Nb	ØD (MM)	(mm)	F2 (mm)	K (mm)	L1 (mm)	L2 (mm)	ØTmini (mm)	(kg)
	<input type="button" value="All"/>	<input type="button" value="All"/>	<input type="button" value="All"/>	<input type="button" value="All"/>	<input type="button" value="All"/>	<input type="button" value="All"/>	<input type="button" value="All"/>	<input type="button" value="All"/>
3616 04 00	4	13	14	14	14	20	12.5	.018
3616 06 00	6	16	17	17.5	17	22	15	.028
3616 08 00	8	18	19	19.5	18.5	23.5	17	.036
3616 10 00	10	22	27	24	21.5	26.5	21	.063
3616 12 00	12	24	24	26	23	27	23	.062
3616 14 00	14	27	27	29.5	25.5	29.5	25	.079