



MOD	LOC	DIST	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
4	BD	35				H	REDRAWN & REV PER ECN BD5454	7-1-92	-
						J	OBS -3 PER EC 0020-0394-93	11/17/94	RK



- 208496-1 MATES WITH RECEPTACLE 208497-1.
208496-3 MATES WITH RECEPTACLE 208497-3.
- AMP PART NUMBER AND DATE CODE TO BE LOCATED APPROX
ON COUPLING RING.
- THIS PLUG ACCEPTS THREE TYPE XII MALE CONTACTS.
MAX WIRE INSULATION DIA = .220.

OBSOLETE	YES	208496-3
	NO	208496-1
	TETRASEAL	PART NO

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± - ANGLES ± - MATERIAL	DR 12-3-92 H MOLL	AMP AMP Incorporated Harrisburg, PA 17105-3608		
	CHK 12-29-92 R.STONE			
	APPD 12-29-92 K.BEAVER	NAME		
SEE CALLOUT	APPD 12-29-92 C.ROHDE	PLUG ASSEMBLY, REVERSE SEX, SERIES 3, 22-3, CMC		
	PRODUCT SPEC 108-10040			
FINISH	APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO
SEE CALLOUT	-	C	00779	C=208496
	WEIGHT -	SCALE	2:1	SHEET 1 OF 1

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.