



Datasheet

ENGLISH

Stock No: 251-8682

RS Pro Female Straight Black Open Top 2 Way 1 Row 2.54mm Pitch



Product Details

RS 2.54mm Low Profile Open Shorting Links

Open shorting links with a 2.54mm pitch, 3A rated bright tin plated phosphor bronze contacts and PBT UL94V-0 housings. These 2.54mm open shorting links are designed to mate with and allow probing of 0.64mm sq headers. Stock numbers [251-8682](#) (black) & [251-8698](#) (red) are 5.97mm high and stock number [251-8569](#) is a low profile open shorting links with a 4.5mm height

Specifications:

Type	Open Top
Number of Contacts	2
Pitch	2.54mm
Gender	Female
Colour	Black
Number of Rows	1
Width	5.97mm
Depth	2.44mm
Contact Material	Phosphor Bronze
Contact Plating	Tin
Orientation	Straight
Maximum Contact Resistance	7mΩ

Dimensions:

