

ENCLOSED HOSE REELS FOR WATER/STAINLESS STEEL

DRF/I series - 304 stainless steel - Polyurethane hose ether base



Part number	Length (m)	Temperature min/max (°C)	Max. operating pressure (bar)	Net weight (Kg)	Profile
DRFI 1012LS	12.00	-15.00 / 65.00	10.00	7,3	WATER

Part number	Dim. A (mm)	Dim. B (mm)	Ø int/ext (mm)
DRFI 1012LS	370.00	337.00	10.00 / 14.00

