



PRODUCT-DETAILS

CPFM16/BL/50M**16MM PE CONDUIT 50M - BL****General Information**

Extended Product Type:	CPFM16/BL/50M
Product ID:	7TCA296000R1766
EAN:	5020963027109
Catalog Description:	16MM PE CONDUIT 50M - BL
Long Description:	Medium Weight Conduit, Nominal Conduit Size 16mm, NW Conduit Size 13, Fine Conduit Pitch, Outside Diameter 15.8mm, Inside Diameter 11.3mm, Static Bend Radius 30mm, Reel Length 50 Meters, Polyester, Black
Display Name:	CPFM16/BL/50M

Additional Information

Product Main Type:	Adaptaflex Flexible Cable Protection
Application:	Indoors / Outdoors, Low Temperature Flexing, High Impact Resistance

Ordering

EAN:	5020963027109
-------------	---------------

UPC: 786210274119

Dimensions

Outside Diameter: 15.8 mm

Technical

Number of Batteries: 0

Color: Black

Material: Polyester

Environmental

WEEE Category: Product Not in WEEE Scope

RoHS Information: Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Container Information

Package Level 1 Units: 1 piece

Package Level 1 EAN: 5020963027109

Package Level 1 Height: 5.91 in
150 mm

Package Level 1 Depth / Length: 17.32 in
440 mm

Package Level 1 Width: 17.32 in
440 mm

Certificates and Declarations

Declaration of Conformity - CE: 9AKK107492A9618

RoHS Declaration: 9AKK107992A8994

REACH Declaration: 9AKK107992A8994

External Classifications and Standards

ETIM 8: EC001175 - Corrugated plastic hose

ETIM 9: EC001175 - Corrugated plastic hose

UNSPSC: 39131706

Categories

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems

