




Connectors > PCB Connectors > PCB Headers & Receptacles > DYNAMIC 2000 HDR ASSY



PCB Connector Type: **PCB Mount Header**

PCB Mount Orientation: **Vertical**

Connector System: **Wire-to-Board**

Number of Positions: **16**

Number of Rows: **2**

[All DYNAMIC 2000 HDR ASSY \(44\)](#)

Features

Product Type Features

PCB Connector Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

PCB Mount Orientation	Vertical
Number of Positions	16
Number of Rows	2

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features



Contact Mating Area Plating Material Thickness	.38 μm[15 μin]
Contact Mating Area Plating Material	Gold (Au)
Contact Type	Pin
Contact Current Rating (Max)	5 A

Termination Features

Termination Method to PCB	Through Hole - Solder
---------------------------	-----------------------

Mechanical Attachment

Mating Retention	With
PCB Mount Retention Type	Retention Leg
Mating Alignment Type	Keyed
PCB Mount Retention	With
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount
Mating Alignment	With

Housing Features

Housing Material	Polyester GF
Centerline (Pitch)	2.5 mm[.099 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Box, Tube
------------------	-----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JAN 2025 (247)
Candidate List Declared Against: JAN 2025 (247)
Does not contain REACH SVHC

Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
-----------------	--

Solder Process Capability

Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1-1318118-8
DYNAMIC D-2100 REC HSG 16P X-KEY


Also in the Series | Dynamic 2000 Series

Connector Contacts(10)

Connector Hardware(3)

Insertion & Extraction Tools(2)

PCB Headers & Receptacles(58)




PCB Terminal Blocks(9)



Power Contacts(10)




Rectangular Power Connectors(53)




Wire-to-Board Headers & Receptacles (58)

Customers Also Bought




TE Part #2040800-1

1mm WIRE TO BOARD EXTERNAL REC ASSY



TE Part #3-179868-0

2.0 AF TAB ASSY 30P B/TRAY



TE Part #2040809-1

1mm WIRE TO BOARD REC ASSY VERTICAL



TE Part #2-292252-8

CT DOUBLE ROW ASSY V 28P HDR N



TE Part #1318126-1

DYNAMIC D2100 HDR V ASSY 12P



TE Part #CAT-D9934-A66

Contact: Component To Wire ; 5A, 28-18 wire size, gold plated



TE Part #5-2176389-1

RQ 1206 357R 0.1% 10PPM 5K RL



TE Part #2-1318118-9

DYNAMIC D2100 REC HSG 20P Y



TE Part #1053398-1

2064 8002 90

Documents

Product Drawings

DYNAMIC D-2100 V-HDR ASS'Y 16P X-KEY SEQ

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1747994-1_A.2d_dxf.zip

1-1747994-1

PCB Mount Header, Vertical, Wire-to-Board, 16 Position, 2.5 mm [.099 in] Centerline, Fully Shrouded, Gold (Au), Dynamic 2000 Series



English

Customer View Model

[ENG_CVM_CVM_1-1747994-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1747994-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Dynamic Connector D-2000 Series

Japanese

[Application Specification](#)

Japanese