



SITOR fuse link, with slotted blade contacts, NH3, In: 400 A, aR, Un AC: 2000 V, Un DC: 440 V, front indicator

Model			
product brand name		SENTRON	
product designation		SITOR fuse link	
design of the product		With slotted blade contacts	
design of an identification indicator		front indicator	
design of the switching contact		with slotted blade contacts for M10 screw fixing. mounting dimension: 210 mm	
design of the fuse link		SITOR, LV HRC design	
General technical data			
size of fuse system according to EN 60269-1		NH3	
operating class of the fuse link		aR	
varying load factor (WL)		1	
type of voltage of the operating voltage		AC/DC	
operating voltage at AC according to UL rated value		2 000 V	
Supply voltage			
supply voltage			
• at AC		2 000 V	
• at DC		440 V	
Breaking Capacity			
switching capacity current			
• according to IEC 60947-2 rated value		100 kA	
Dissipation			
power loss [W]		150 W	
power loss [W]			
• for rated value of the current at AC in hot operating state per pole		150 W	
• maximum		150 W	
Product details			
product description		with blade contacts, silver-plated	
accessories included		no	
Mechanical Design			
mounting position		Any, preferably vertical	
Environmental conditions			
ambient temperature during operation			
• minimum		-20 °C	
• maximum		50 °C	
environmental category		-20 to +50 at 95% relative humidity	
Approvals Certificates			
General Product Approval		Test Certificates	other



EG-Konf.



UR



[Special Test Certificate](#)

[Confirmation](#)

Environment

[Environmental Conformations](#)

[Environmental Conformations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NE7432-0U>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3NE7432-0U>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NE7432-0U

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

4/4/2025 

