

DATA SHEET

MMCPLO6AFS

Full shielded CAT6A tool less RJ45 plug



- Tool less opening and closing
- Class Ea performance
- Suitable for AWG22 cables







DESCRIPTION / APPLICATIONS

The MMCPLO6AFS CAT6A shielded RJ45 plug is designed for direct connection of IP equipment.

- Fitted with a clamping ring at the rear to hold the cable securely in place
- It Meets the requirements of class Ea and the latest PoE standard.
- Tool less assembly and connection.
- Suitable for LAN and MAN applications up to 10 Gbits Ethernet (IEEE 802.3an).

PERFORMANCES ———

CONNECTOR	SYSTEM
60603-7-51 Cat6A	TIA 568-C.2
FCC Part 68 subpart F	ISO 11801 Ed2.2 Class Ea - EN 50173-1
UL 18663	IEEE 802.3 af, at et bt (PoE / PoE+ / 4PPoE)





DATA SHEET

TECHNICAL PROPERTIES

Cable type: Stranded AWG26 to AWG24 Dimensions: 57 x 11,6 x 14,4 mm (H x W x D)

Solid AWG26 to AWG22 Body: Zamac 360°

Cable diameter: 5,5 mm to 8,5 mm. Contacts: Phosphor - Bronze

Conductors diameter: 1,5 mm Max. Color code: TIA 568B

ELECTRICAL PROPERTIES

Contact resistance : $\leq 100 \text{ m}\Omega$

Insulation resistance : $\geq 1000 \text{ M}\Omega \text{ to } 500 \text{ Vdc}$

Voltage rating: 125 Vac RMS

Insertion cycle: > 750
Operating voltage: < 72V Dc
Power rating: 90 W (4PPoE)

ORDERING INFORMATION

PART NUMBER	DESCRIPTION	PACKING
MMCPL06AFS	Full shielded CAT6A tool less RJ45 plug	Unit