



Part Number : [190440140](#)
Product Description : Krimptite Ring Tongue
Terminal for 16-14 AWG, Stud Size 3/8", 32.51mm
Length, Carton
Series Number : 19044
Status : Active
Product Category : Ring and Spade Terminals
Engineering Number : B-101-38HD



Documents & Resources

Drawings

[190440140 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)


[Creo](#)

Specifications

[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19044
Description	Krimptite Ring Tongue Terminal for 16-14 AWG, Stud Size 3/8", 32.51mm Length, Carton
Comments	Heavy Duty
Keyword	Ring Terminal, Ring Terminals
Product Name	Krimptite
Type	Ring
UPC	800755060164

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	3.919/g
Packaging Type	Carton
Plating min - Mating	2.540µm

Plating min - Termination	2.540µm
Stud Size	3/8" (M9)
Termination Interface Style	Crimp or Compression
Wire Size (AWG)	14, 16
Wire Size mm ²	1.30-2.00

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 22-10 AWG and 6.0mm ² - 0.5mm ²	<u>640030100</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640070100</u>
ServiceGrade Hand Crimp Tool - Ratchet	<u>640160038</u>