

Actuator

45-
2F40.1010.000

Distribution by
Rs-online



<https://rs-online.eao.com/p/45-2F40.1010.000>

Your product:



45-2F40.1010.000

Actuator

FRONT

Front dimension:	Ø 29,5 mm
Front form:	Round
Front bezel colour:	Black
Front bezel material:	Plastic

MOUNTING

Design:	Raised
Mounting cut-out:	Ø 22.3 mm
Mounting type:	Panel mounting

OPERATING-/INDICATION PART

Lever colour:	Black
Lever material:	plastic

MECHANICAL CHARACTERISTIC

Switching action:	Momentary
Mechanical lifetime:	250 000 cycles of operation per direction of actuation
Weight:	0.085 kg

AMBIENT CONDITION

Operating temperature:	- 25 °C ... + 70 °C
Storage temperature:	- 40 °C ... + 80 °C

Shock resistance:

According to IEC 60068-2-27: Sinusoidal half-wave 50 g / 11 ms

Vibration resistance:

According to IEC 60068-2-6: 10 ... 500 Hz: 5 g

Climate resistance:

During operation according to IEC 60721: 3K6, 3C3, 3S2, 3M6, 3B2

CERTIFICATE**REACH:**

REACH compliant

RoHS:

RoHS compliant

OTHER**Short Description:**

Actuator, Ø 22.3 mm, Ø 29,5 mm, Black, Round, Black, Plastic, Momentary

Housing material:



Plastic

Product attributes:

2 positions (U-D), lockable

Hints:

Lockable only in center position

Wiring diagrams:**Mounting cut-outs:****Dimension drawings:**

