

## **PLUGS and LEADS**




TYPE	Length L
143(3) or (4) 0.61 AC	610mm
143(3) or (4) 1.00 AC	1 metre
143(3) or (4) 1.50 AC	1.5 metres
143(3) or (4) 3.00 AC	3 metres

Plug and Lead black sheathed twin cable with blue/brown colour-coded wires for use on AC supplies.




TYPE	Length L
143(3) or (4) 0.61 DC	610mm
143(3) or (4) 1.00 DC	1 metre
143(3) or (4) 1.50 DC	1.5 metres
143(3) or (4) 3.00 DC	3 metres

Plug and Lead black sheathed twin cable with red/black colour-coded wires for use on DC supplies. Polarity markings +/- on connection head.




TYPE	Length L
1434 L0.61 AC	610mm
1434 L1.00 AC	1 metre

Plug and Lead black sheathed twin cable with blue/brown colour-coded wires for use on AC supplies. Right-angle connection head as illustrated. Only available to suit 2.8 x 0.5 pins. UL and CSA listed.



TYPE	Length L
1434 L0.61 DC	610mm
1434 L1.00 DC	1 metre

Plug and Lead black sheathed twin cable with red/black colour-coded wires for use on DC supplies. Right-angle head with +/- polarity markings. Only available to suit 2.8 x 0.5 pins. UL and CSA listed.



TYPE	Length L
143(3) or (4) E 0.61 AC	610mm
143(3) or (4) E 1.00 AC	1 metre
143(3) or (4) E 1.50 AC	1.5 metres
143(3) or (4) E 3.00 AC	3 metres

Plug and Lead black sheathed 3 core cable, colour-coded brown/blue/green-yellow, for use on AC supplies. Earth wire brought out with M4 Ring terminal provided for connection to the earthing point on the EBM fan.