



DX4 DETACHABLE HOLSTER POCKET TROUSERS

DESCRIPTION

The DX4 Holster Trousers are ergonomically designed and use the targeted placement of dynamic 4X stretch fabrics to give maximum range of movement when working. The trousers feature a high-rise back waistband with side elastication, ensuring protection in all working positions. Pre-bent top loading adjustable knee pad pockets, generously sized front pockets and multi-functional zip thigh pockets offer secure storage of phone, pens and tools. Triple stitching throughout for maximum durability.

COMPOSITION

-  **Titanmill Pro Stretch: 93% Polyester, 7% Elastane, 270g**
-  **65% Polyester, 35% Cotton Ripstop Weft Stretch, 230g**
-  **CorePro: 87% Nylon, 13% Elastane, 245g**
-  **White/Grey 28-48**

FEATURES

- 4-way stretch fabric for ease of movement and added comfort
- High rise back waistband ensures protection in all working positions
- Reflective trim for increased visibility and safety
- Zip off holster pockets for added versatility
- Two tier knee pad pockets allowing two positioning options
- Multiple side zip compartments for secure storage
- 16 pockets for ample storage
- 2 side zip pockets for secure storage
- Smart phone pocket
- Hammer loop for secure storage of work tools
- 2 Back pockets
- 2 Zipped thigh pockets

STANDARDS

EN 14404: 2004 + A1: 2010 Type 2 Level 0 (When used in combination with S156)

COLOUR / SIZES

SKU	COLOUR	SIZE RANGE
DX440WGR	WHITE/GREY	28-14

FEATURES



HALF ELASTICATED WAIST
Half elasticated waist for a secure and comfortable fit



UPF 40+
40+ UPF rated fabric to block 98% of UV rays



16 POCKETS
16 pockets for ample storage



TECHINCAL INFORMATION



- Do not iron the reflective tape
- Wash dark colours separately
- Wash garment inside out
- Wash garment inside out and fully fastened
- Wash reflective tape on the inside
- Wash with similar colours

Item	Colour Fit	Len (cm)	Wid (cm)	Hgt (cm)	Weight (Kg)	Cubic (m³)	EAN13	GTIN/DUN14
DX440WGR28	White/Grey	65	45	36	1.147	5850.000	5036108366194	15036108855213
DX440WGR30	White/Grey	65	45	36	1.165	5850.000	5036108366200	15036108855220
DX440WGR32	White/Grey	65	45	36	1.177	5850.000	5036108366217	15036108855237
DX440WGR33	White/Grey	65	45	36	1.202	5850.000	5036108366224	15036108855244
DX440WGR34	White/Grey	65	45	36	1.213	5850.000	5036108366231	15036108855251
DX440WGR36	White/Grey	65	45	36	1.224	5850.000	5036108366248	15036108855268
DX440WGR38	White/Grey	65	45	36	1.238	5850.000	5036108366255	15036108855275
DX440WGR40	White/Grey	65	45	36	1.249	5850.000	5036108366262	15036108855282
DX440WGR41	White/Grey	65	45	36	1.300	5850.000	5036108366279	15036108855299
DX440WGR42	White/Grey	65	45	36	1.286	5850.000	5036108366286	15036108855305
DX440WGR44	White/Grey	65	45	36	1.290	5850.000	5036108366293	15036108855312
DX440WGR46	White/Grey	65	45	36	1.307	5850.000	5036108366309	15036108855329
DX440WGR48	White/Grey	65	45	36	1.327	5850.000	5036108366316	15036108855336