

Datasheet

RS Pro 85dB sound PCB Mount Continuous Internal Buzzer, 2400 → 3400 Hz

RS Stock No: **622-1354**



Product Details

RS Pro internal piezo buzzer operates at a voltage range of 3 - 24 V dc. This continuous buzzer delivers 85 dB sound at a frequency range of 2400 - 3400 Hz. It is suitable for applications that require high sound output.

Features and Benefits

- Circular cased PCB mounting
- High sound output buzzers
- Continuous delivery

**Specifications:**

Drive Type	Internal
Mounting Type	PCB
Tone Type	Continuous
Diameter	23.8 mm
Dimensions	23.8 (dia.) x 16 mm
Height	16 mm
Maximum Frequency	3400 Hz
Maximum Operating Temperature	+85°C
Maximum Supply Voltage	20 V dc
Minimum Frequency	2400 Hz
Minimum Operating Temperature	-30°C
Minimum Supply Voltage	3 V dc
Sound Level	85 dB
Supply Current	8 mA