

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,-.

© COPYRIGHT 2011APR BY-Tyco Electronics Japan G.K.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD


D

REVISED

25APR11

MM



NY









NOTES


1 MATERIAL:HOUSING:GLASS FILED THERMO PLASTIC
,POLYESTER(94V-0),
COLOR:1-/2- : BLACK
: 9- : NATURAL

2 TO COAT ALL SURFACE OF HOUSING WITH TEFLON




 KEYING:Y 2-1318118-9 9-1318118-9		 KEYING:Y 2-1318118-8		 KEYING:Y 2-1318118-6 9-1318118-6	
 KEYING:X 1-1318118-9		 KEYING:X 1-1318118-8		 KEYING:X 1-1318118-6	

OBSOLETE	2	5.58	26.4	25.8	22.5	9	20	5-1318118-9
	-	5.58	26.4	25.8	22.5	9	20	9-1318118-9 2-1318118-9
	-	5.58	26.4	25.8	22.5	9	20	1-1318118-9
	-	4.69	21.4	20.8	17.5	7	16	2-1318118-8
	-	4.69	21.4	20.8	17.5	7	16	1-1318118-8
OBSOLETE	2	3.8	16.4	15.8	12.5	5	12	5-1318118-6
	-	3.8	16.4	15.8	12.5	5	12	3-1318118-6
	-	3.8	16.4	15.8	12.5	5	12	9-1318118-6 2-1318118-6
	-	3.8	16.4	15.8	12.5	5	12	1-1318118-6
FINISH	NET WEIGHT(g)	C	B	A	N	POS	PART NUMBER	



KEY LOCATION VIEW
2-1318118-6
9-1318118-6
(KEYING Y)

DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED		DWN K.IKEDA 7/DEC/'98 CHK N.MATSUBARA 7/DEC/'98 APVD I.HASEGAWA 7/DEC/'98 PRODUCT SPEC		TE Connectivity	
		10: ±0.3 30: >10 ±0.35 100: >30 ±0.4 ANGLE: ±3°		108-5619		DOUBLE ROW REC HSG <DYNAMIC D-2100D>	
MATERIAL 1		FINISH		114-5258		SIZE A3	CAGE CODE 00779
CUSTOMER DRAWING		WEIGHT		DRAWING NO C-1318118		RESTRICTED TO -	
				SCALE 4-1		SHEET 1	OF 1
						REV D	