



Type 57683
Designation..... Eco Charger Recycled Pro

System to charge NiMH (Nickel Metal Hydride)
Cell sizes AAA or AA
Cell configuration..... 1-4 cells (single slot charging) AA or AAA

Charge Indicator..... green LED
 charging blinking slow
 defective/wrong cell blinking fast
 charging complete solid green

Input..... 5V = 1...3A / 5...15W
Plug/cable length..... USB C Plug / 1m USB C to USB C cable included

Safety Features Wrong cell (alkaline) detection
 Wrong polarity detection (mechanical)
 Short circuit detection
 Low input voltage detection

Charging currents and cut off Timer.....

3A Source
 AA: 1-2 2000mA / 1.7h
 AA: 3-4 1000mA / 3.5h
 AAA: 1-4 1000mA / 1.5h

5V/2A Source
 AA: 1-2 1400mA / 2.5h
 AA: 3-4 700mA / 5h
 AAA: 1-4 700mA / 2h

5V/1A Source
 AA: 1-2 500mA / 7h
 AA: 3-4 350mA / 10h
 AAA: 1-4 350mA / 4h

Maintenance charge current.....
 AAA 50mA for 1h
 AA 100mA for 1h

Charge Termination -dV and temperature cut off

Housing Material..... ABS

Housing colour Light Grey/Green

Dimensions

Length 125.5 ± 1 mm
 Width 73.5 ± 1 mm
 Height 28.1 ± 1mm
 Weight 91 ± 3g

Charger:

No publication or circulation of data to third parties without consent of VARTA Consumer Batteries