



Product availability: Stock - Normally stocked in distribution facility



## Main

Commercial Status	Commercialised
Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch lever
Device short name	ZCY
Product compatibility	XCKD XCKP XCKT XCMD
Associated head	ZCE01 ZCE05
Movement of operating head	Rotary
Type of operator	Rod lever spring return glass fiber (round rod 3 mm, L = 125 mm)
Tracks	No track
Type of approach	Lateral approach

## Complementary

Switch actuation	By any moving part
Positive opening	Without

## Environment

Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

## Ordering and shipping details

Category	22418 - LIMIT SWITCH,IEC,XCKP&XCKT
Discount Schedule	T
GTIN	00785901502548
Nbr. of units in pkg.	1
Package weight(Lbs)	0.06
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	ID

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS	Compliant - since 0851 - <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available <a href="#">Download Product Environmental</a>
Product end of life instructions	Available <a href="#">Download End Of Life Manual</a>

## Contractual warranty

---

Period	18 months
--------	-----------

---