

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

Product form : Mixture  
Trade name : RTD Chlorine Free Spray  
UFI : 74A0-M04A-400R-FNRT  
Vaporizer : Aerosol

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

##### 1.2.1. Relevant identified uses

Main use category : Professional use, Industrial use  
Industrial/Professional use spec : For professional use only  
Industrial  
Use of the substance/mixture : Lubricants, Greases and Release Products

##### 1.2.2. Uses advised against

No additional information available

#### 1.3. Details of the supplier of the safety data sheet

##### Manufacturer

ROCOL a division of ITW Ltd  
Rocol House  
Wakefield Rd, Swillington  
LS26 8BS Leeds - United Kingdom  
T +44 (0)113 232 2600  
[customer.service@rocol.com](mailto:customer.service@rocol.com) - [www.rocol.com](http://www.rocol.com)

#### 1.4. Emergency telephone number

Emergency number : +44 (0)113 232 2600

Country	Organisation/Company	Address	Emergency number	Comment
United Kingdom	National Poisons Information Service (Birmingham Centre) City Hospital	Dudley Road B18 7QH Birmingham	0344 892 0111	

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

##### Classification according to Regulation (EC) No. 1272/2008 [CLP]

Aerosol, Category 1 H222;H229  
Hazardous to the aquatic environment — Chronic Hazard, Category 3 H412  
Full text of H statements : see section 16

##### Adverse physicochemical, human health and environmental effects

No additional information available

#### 2.2. Label elements

##### Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP) :



GHS02

# RTD Chlorine Free Spray

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Signal word (CLP)	: Danger
Hazard statements (CLP)	: H222 - Extremely flammable aerosol. H229 - Pressurised container: May burst if heated. H412 - Harmful to aquatic life with long lasting effects.
Precautionary statements (CLP)	: P410+P412 - Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F. P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. P211 - Do not spray on an open flame or other ignition source. P251 - Do not pierce or burn, even after use. P271 - Use only outdoors or in a well-ventilated area. P280 - Wear protective gloves/protective clothing/eye protection/face protection/hearing protection.

### 2.3. Other hazards

No additional information available

## SECTION 3: Composition/information on ingredients

### 3.1. Substances

Not applicable

### 3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
HYDROCARBON AEROSOL PROPELLANT (<0.1% 1,3-BUTADIENE) substance with national workplace exposure limit(s) (GB)	(CAS-No.) 68476-85-7 (EC-No.) 270-704-2	15 – 30	Flam. Gas 1, H220 Press. Gas (Liq.), H280 Flam. Liq. 1, H224 Muta. Not classified Carc. Not classified
ALCOHOLS C16-C18, C18-UNSATURATED, ETHOXYLATED	(CAS-No.) 68920-66-1 (EC-No.) 500-236-9 (REACH-no) 01-2119489407-26	1 – 2.4	Skin Irrit. 2, H315 Aquatic Acute 1, H400 Aquatic Chronic 3, H412

Product subject to CLP Article 1.1.3.7. The disclosure rules of the components is modified in this case.

Full text of H-statements: see section 16

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

First-aid measures general	: Never give anything by mouth to an unconscious person. If you feel unwell, seek medical advice (show the label where possible).
First-aid measures after inhalation	: Allow affected person to breathe fresh air. Allow the victim to rest.
First-aid measures after skin contact	: Wash skin with plenty of water.
First-aid measures after eye contact	: Rinse immediately with plenty of water. Obtain medical attention if pain, blinking or redness persists.
First-aid measures after ingestion	: Rinse mouth. Do NOT induce vomiting. Obtain emergency medical attention.

### 4.2. Most important symptoms and effects, both acute and delayed

Symptoms/effects	: Not expected to present a significant hazard under anticipated conditions of normal use.
------------------	--

### 4.3. Indication of any immediate medical attention and special treatment needed

No additional information available

# RTD Chlorine Free Spray

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### SECTION 5: Firefighting measures

#### 5.1. Extinguishing media

Suitable extinguishing media : Foam. Dry powder. Carbon dioxide. Water spray. Sand.  
Unsuitable extinguishing media : Do not use a heavy water stream.

#### 5.2. Special hazards arising from the substance or mixture

No additional information available

#### 5.3. Advice for firefighters

Firefighting instructions : Use water spray or fog for cooling exposed containers. Exercise caution when fighting any chemical fire. Prevent fire fighting water from entering the environment.  
Protection during firefighting : Do not enter fire area without proper protective equipment, including respiratory protection.

### SECTION 6: Accidental release measures

#### 6.1. Personal precautions, protective equipment and emergency procedures

##### 6.1.1. For non-emergency personnel

Emergency procedures : Evacuate unnecessary personnel.

##### 6.1.2. For emergency responders

Protective equipment : Equip cleanup crew with proper protection.  
Emergency procedures : Ventilate area.

#### 6.2. Environmental precautions

Prevent entry to sewers and public waters. Notify authorities if liquid enters sewers or public waters. Avoid release to the environment.

#### 6.3. Methods and material for containment and cleaning up

Methods for cleaning up : Soak up spills with inert solids, such as clay or diatomaceous earth as soon as possible. Collect spillage. Store away from other materials.

#### 6.4. Reference to other sections

See Heading 8. Exposure controls and personal protection.

### SECTION 7: Handling and storage

#### 7.1. Precautions for safe handling

Precautions for safe handling : Wash hands and other exposed areas with mild soap and water before eating, drinking or smoking and when leaving work. Provide good ventilation in process area to prevent formation of vapour.

#### 7.2. Conditions for safe storage, including any incompatibilities

Storage conditions : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Keep container closed when not in use.  
Incompatible products : Strong bases. Strong acids.  
Incompatible materials : Sources of ignition. Direct sunlight.

#### 7.3. Specific end use(s)

No additional information available

# RTD Chlorine Free Spray

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### SECTION 8: Exposure controls/personal protection

#### 8.1. Control parameters

##### 8.1.1 National occupational exposure and biological limit values

HYDROCARBON AEROSOL PROPELLANT (<0.1% 1,3-BUTADIENE) (68476-85-7)	
United Kingdom - Occupational Exposure Limits	
Local name	Liquefied petroleum gas
WEL TWA (OEL TWA) [1]	1750 mg/m <sup>3</sup>
WEL TWA (OEL TWA) [2]	1000 ppm
WEL STEL (OEL STEL)	2180 mg/m <sup>3</sup>
WEL STEL (OEL STEL) [ppm]	1250 ppm
Remark (WEL)	Carc (Capable of causing cancer and/or heritable genetic damage (only applies if LPG contains more than 0.1% of buta-1,3-diene))
Regulatory reference	EH40/2005 (Fourth edition, 2020). HSE

##### 8.1.2. Recommended monitoring procedures

No additional information available

##### 8.1.3. Air contaminants formed

No additional information available

##### 8.1.4. DNEL and PNEC

No additional information available

##### 8.1.5. Control banding

No additional information available

#### 8.2. Exposure controls

##### 8.2.1. Appropriate engineering controls

No additional information available

##### 8.2.2. Personal protection equipment

###### Personal protective equipment:

Avoid all unnecessary exposure.

###### 8.2.2.1. Eye and face protection

<b>Eye protection:</b>
Chemical goggles or safety glasses

###### 8.2.2.2. Skin protection

<b>Hand protection:</b>
Wear protective gloves. Nitrile rubber gloves

###### 8.2.2.3. Respiratory protection

<b>Respiratory protection:</b>
In case of inadequate ventilation wear respiratory protection. Wear a respirator conforming to EN140 with Type A filter or better

###### 8.2.2.4. Thermal hazards

No additional information available

# RTD Chlorine Free Spray

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### 8.2.3. Environmental exposure controls

#### Other information:

Do not eat, drink or smoke during use.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Colour	: red.
Odour	: Characteristic odour.
Odour threshold	: No data available
pH	: No data available
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: No data available
Freezing point	: No data available
Boiling point	: < 0 °C
Flash point	: < -60 °C
Auto-ignition temperature	: ≥ 200 °C
Decomposition temperature	: No data available
Flammability (solid, gas)	: Non flammable.
Vapour pressure	: No data available
Relative vapour density at 20 °C	: No data available
Relative density	: No data available
Solubility	: insoluble in water.
Partition coefficient n-octanol/water (Log Pow)	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available
Explosive properties	: No data available
Oxidising properties	: No data available
Explosive limits	: No data available

### 9.2. Other information

VOC content : 168 g/l

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

Extremely flammable aerosol.

### 10.2. Chemical stability

Not established.

### 10.3. Possibility of hazardous reactions

Not established.

### 10.4. Conditions to avoid

Direct sunlight. Extremely high or low temperatures.

### 10.5. Incompatible materials

Strong acids. Strong bases.

### 10.6. Hazardous decomposition products

fume. Carbon monoxide. Carbon dioxide.

# RTD Chlorine Free Spray

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### SECTION 11: Toxicological information

#### 11.1 Information on toxicological effects

Acute toxicity (oral) : Not classified  
Acute toxicity (dermal) : Not classified  
Acute toxicity (inhalation) : Not classified

#### ALCOHOLS C16-C18, C18-UNSATURATED, ETHOXYLATED (68920-66-1)

LD50 oral rat	> 2000 mg/kg
---------------	--------------

#### HYDROCARBON AEROSOL PROPELLANT (<0.1% 1,3-BUTADIENE) (68476-85-7)

LC50 Inhalation - Rat (Vapours)	> 20 mg/l/4h
---------------------------------	--------------

Skin corrosion/irritation : Not classified  
Additional information : Based on available data, the classification criteria are not met  
Serious eye damage/irritation : Not classified  
Additional information : Based on available data, the classification criteria are not met  
Respiratory or skin sensitisation : Not classified  
Additional information : Based on available data, the classification criteria are not met  
Germ cell mutagenicity : Not classified  
Additional information : Based on available data, the classification criteria are not met  
Carcinogenicity : Not classified  
Additional information : Based on available data, the classification criteria are not met

Reproductive toxicity : Not classified  
Additional information : Based on available data, the classification criteria are not met

STOT-single exposure : Not classified  
Additional information : Based on available data, the classification criteria are not met

STOT-repeated exposure : Not classified  
Additional information : Based on available data, the classification criteria are not met

Aspiration hazard : Not classified  
Additional information : Based on available data, the classification criteria are not met

#### RTD Chlorine Free Spray

Vaporizer	Aerosol
-----------	---------

Potential adverse human health effects and symptoms : Based on available data, the classification criteria are not met

### SECTION 12: Ecological information

#### 12.1. Toxicity

Ecology - water : Harmful to aquatic life with long lasting effects.  
Hazardous to the aquatic environment, short-term (acute) : Not classified  
Hazardous to the aquatic environment, long-term (chronic) : Harmful to aquatic life with long lasting effects.

#### ALCOHOLS C16-C18, C18-UNSATURATED, ETHOXYLATED (68920-66-1)

LC50 - Fish [1]	10 – 100 mg/l
-----------------	---------------

# RTD Chlorine Free Spray

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### 12.2. Persistence and degradability

#### RTD Chlorine Free Spray

Persistence and degradability	May cause long-term adverse effects in the environment.
-------------------------------	---

### 12.3. Bioaccumulative potential

#### RTD Chlorine Free Spray

Bioaccumulative potential	Not established.
---------------------------	------------------

### HYDROCARBON AEROSOL PROPELLANT (<0.1% 1,3-BUTADIENE) (68476-85-7)

Partition coefficient n-octanol/water (Log Pow)	2.3 – 2.8
---	-----------

### 12.4. Mobility in soil

No additional information available

### 12.5. Results of PBT and vPvB assessment

No additional information available

### 12.6. Other adverse effects

Additional information : Avoid release to the environment.

## SECTION 13: Disposal considerations






### 13.1. Waste treatment methods

Product/Packaging disposal recommendations : Dispose in a safe manner in accordance with local/national regulations. Dispose of contents/container to hazardous or special waste collection point, in accordance with local, regional, national and/or international regulation.

Ecology - waste materials : Avoid release to the environment.

## SECTION 14: Transport information

In accordance with ADR / IMDG / IATA / ADN / RID

ADR	IMDG	IATA	ADN	RID
<b>14.1. UN number</b>				
UN 1950	UN 1950	UN 1950	UN 1950	UN 1950
<b>14.2. UN proper shipping name</b>				
AEROSOLS	AEROSOLS	Aerosols, flammable	AEROSOLS	AEROSOLS
<b>Transport document description</b>				
UN 1950 AEROSOLS, 2.1, (D)	UN 1950 AEROSOLS, 2.1	UN 1950 Aerosols, flammable, 2.1	UN 1950 AEROSOLS, 2.1	UN 1950 AEROSOLS, 2.1
<b>14.3. Transport hazard class(es)</b>				
2.1	2.1	2.1	2.1	2.1
				

# RTD Chlorine Free Spray

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

14.4. Packing group				
Not applicable	Not applicable	Not applicable	Not applicable	Not applicable
14.5. Environmental hazards				
Dangerous for the environment : No	Dangerous for the environment : No Marine pollutant : No	Dangerous for the environment : No	Dangerous for the environment : No	Dangerous for the environment : No
No supplementary information available				

### 14.6. Special precautions for user

#### Overland transport

Classification code (ADR) : 5F  
Special provisions (ADR) : 190, 327, 344, 625  
Limited quantities (ADR) : 1I  
Excepted quantities (ADR) : E0  
Packing instructions (ADR) : P207, LP200  
Special packing provisions (ADR) : PP87, RR6, L2  
Mixed packing provisions (ADR) : MP9  
Transport category (ADR) : 2  
Special provisions for carriage - Packages (ADR) : V14  
Special provisions for carriage - Loading, unloading and handling (ADR) : CV9, CV12  
Special provisions for carriage - Operation (ADR) : S2  
Tunnel restriction code (ADR) : D

#### Transport by sea

Special provisions (IMDG) : 63, 190, 277, 327, 344, 381, 959  
Packing instructions (IMDG) : P207, LP200  
Special packing provisions (IMDG) : PP87, L2  
EmS-No. (Fire) : F-D  
EmS-No. (Spillage) : S-U  
Stowage category (IMDG) : None  
Stowage and handling (IMDG) : SW1, SW22  
Segregation (IMDG) : SG69

#### Air transport

PCA Excepted quantities (IATA) : E0  
PCA Limited quantities (IATA) : Y203  
PCA limited quantity max net quantity (IATA) : 30kgG  
PCA packing instructions (IATA) : 203  
PCA max net quantity (IATA) : 75kg  
CAO packing instructions (IATA) : 203  
CAO max net quantity (IATA) : 150kg  
Special provisions (IATA) : A145, A167, A802  
ERG code (IATA) : 10L

#### Inland waterway transport

Classification code (ADN) : 5F  
Special provisions (ADN) : 190, 327, 344, 625  
Limited quantities (ADN) : 1 L  
Excepted quantities (ADN) : E0  
Equipment required (ADN) : PP, EX, A  
Ventilation (ADN) : VE01, VE04  
Number of blue cones/lights (ADN) : 1

#### Rail transport

Classification code (RID) : 5F  
Special provisions (RID) : 190, 327, 344, 625  
Limited quantities (RID) : 1L  
Excepted quantities (RID) : E0  
Packing instructions (RID) : P207, LP200  
Special packing provisions (RID) : PP87, RR6, L2  
Mixed packing provisions (RID) : MP9  
Transport category (RID) : 2



# RTD Chlorine Free Spray

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Special provisions for carriage – Packages (RID) : W14  
Special provisions for carriage - Loading, unloading and handling (RID) : CW9, CW12  
Colis express (express parcels) (RID) : CE2  
Hazard identification number (RID) : 23

### 14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

## SECTION 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

#### 15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions  
Contains no substance on the REACH candidate list  
Contains no REACH Annex XIV substances  
Contains no substance subject to Regulation (EU) No 649/2012 of the European Parliament and of the Council of 4 July 2012 concerning the export and import of hazardous chemicals.  
Contains no substance subject to Regulation (EU) No 2019/1021 of the European Parliament and of the Council of 20 June 2019 on persistent organic pollutants

VOC content : 168 g/l

#### 15.1.2. National regulations

No additional information available

### 15.2. Chemical safety assessment

No chemical safety assessment has been carried out

## SECTION 16: Other information

Data sources : REGULATION (EC) No 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006.  
Other information : None.

Full text of H- and EUH-statements:	
Aquatic Acute 1	Hazardous to the aquatic environment — Acute Hazard, Category 1
Aquatic Chronic 3	Hazardous to the aquatic environment — Chronic Hazard, Category 3
Carc. Not classified	Carcinogenicity Not classified
Flam. Gas 1	Flammable gases, Category 1
Flam. Liq. 1	Flammable liquids, Category 1
Muta. Not classified	Germ cell mutagenicity Not classified
Press. Gas (Liq.)	Gases under pressure : Liquefied gas
Skin Irrit. 2	Skin corrosion/irritation, Category 2
H220	Extremely flammable gas.
H222	Extremely flammable aerosol.
H224	Extremely flammable liquid and vapour.
H229	Pressurised container: May burst if heated.
H280	Contains gas under pressure; may explode if heated.

# RTD Chlorine Free Spray

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

H315	Causes skin irritation.
H400	Very toxic to aquatic life.
H412	Harmful to aquatic life with long lasting effects.

Safety Data Sheet (SDS), EU

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.