



Cut



Heat



Medium Duty

Versatile abrasion-resistant gloves, designed with nitrile coating for enhanced grip

- **Increased durability:** HyFlex® 11-550 assembly gloves feature FORTIX™ Abrasion Resistance nitrile foam coating, achieving EN and ANSI/ISEA 105-2024 ABRASION LEVEL 4
- **Enhanced grip:** The same nitrile foam formulation ensures secure grip in dry or slightly oily conditions, preventing workplace injuries
- **Heightened defenses:** HyFlex® 11-550 industrial working gloves' INTERCEPT™ Cut Resistance Technology fiber also provides entry-level cut protection
- **Specialized protection:** HyFlex® 11-550 safety gloves offer heat protection up to 212°F/100C°
- **Elevated comfort:** These PPE gloves' blend of Para-Aramid®, Spandex® and nylon liner delivers personal protection with supple all-day comfort
- **Considered aesthetics:** Black, dirt-masking palm coating ensures lasting wear



Industries

- Automotive
- Machinery and Equipment
- Metal fabrication

Applications

- General maintenance
- Maintenance inspection
- Handling of glass sheets, sharp edged objects
- Plastic injections
- Molding

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-550

Longer lasting cut protection with
INTERCEPT™ Technology

Key Features

- **FORTIX™ Abrasion Resistance:** Up to 75% greater durability*
- **Nitrile foam coating:** Industrial gloves that deliver secure grip
- **INTERCEPT™ Cut Resistance fiber:** Basic cut protection capabilities
*when compared with similarly equipped competitor gloves

Technologies

 **FORTIX™**
Abrasion Resistance Technology

 **INTERCEPT™**
Cut Resistance Technology

Performance Standards & Regulatory Compliance



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex® 11-550	Finishing: Palm Coated Coating Material: Nitrile Liner Material: Para-aramid, Nylon, Spandex Cuff Style: Knitwrist	15	6, 7, 8, 9, 10	196-248 mm; 7.7-9.8 inches	Black	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

Ansell