

WatchGuard[®] Firebox[®] T10

PROTECT WHERE YOU CONNECT

RETHINK THE PERIMETER

Ideal for small office/home office and small retail environments, the Firebox T10 creates a secure network perimeter in remote locations that do not have adequate security protection in place today. Comprehensive Unified Threat Management (UTM) safeguards intellectual property and protects personal data, credit card numbers, and other critical assets from exposure and theft.

THE BENEFITS OF UTM

An all-in-one network security solution integrates complete protection. All security capabilities work together for a comprehensive approach to network protection with a single console for reporting.

"The ability to leverage the power of a UTM solution like the Firebox T10 in remote locations, and manage them from a single, central console gives IT a powerful tool for administering and enforcing policy."

*Mike Jude
Principle Analyst
Frost & Sullivan*

BEST-OF-BREED SECURITY

- Application-layer content inspection recognizes and blocks threats that stateful packet firewalls cannot detect.
- Powerful subscription-based security services boost protection in critical attack areas for multiple layers of defense. By partnering with leading technology providers, WatchGuard is able to integrate best-of-breed security components into one Unified Threat Management platform for stronger security at big cost savings.
 - **APT Blocker** uses a cloud-based sandbox with full system emulation to detect and block advanced malware and zero day attacks.
 - **Application Control** keeps unproductive, inappropriate, and dangerous applications off-limits.
 - **Intrusion Prevention Service (IPS)** delivers in-line protection from malicious exploits, including buffer overflows, SQL injections, and cross-site scripting attacks.
 - **WebBlocker** controls access to sites that host objectionable material or pose network security risks.
 - **Gateway AntiVirus (GAV)** scans traffic on all major protocols to stop threats.
 - **spamBlocker** delivers continuous protection from unwanted and dangerous email.
 - **Reputation Enabled Defense** ensures faster, safer web surfing with cloud-based reputation look-up.
 - **Data Loss Prevention (DLP)** automatically inspects data in motion for corporate policy violations.
- Multiple VPN choices (IPSec, SSL, L2TP) for secure remote access include support for Android and Apple iOS devices.

EASY TO MANAGE

- Interactive, real-time monitoring and reporting – at no additional charge – give an unprecedented view into network security activity so you can take immediate preventive or corrective actions.
- **WatchGuard Dimension™**, a public and private cloud-ready visibility solution, instantly turns raw data into security intelligence.
- **RapidDeploy™** technology enables quick, secure configuration at remote locations without technical staff on-site.
- Intuitive management console centrally manages all security functions.
- Extend best-in-class UTM security to the WLAN by adding WatchGuard's Wireless Access Points.
- Drag-and-drop Branch Office VPN setup – three clicks and your remote office is connected.

HIGHEST UTM PERFORMANCE IN THE INDUSTRY

- Firewall throughput of up to 200 Mbps and UTM throughput of 55 Mbps to keep traffic moving.
- No need to compromise protection for strong performance or vice versa. Multi-layered, interlocking security protects the network while throughput remains high.
- Gigabit Ethernet ports support high-speed LAN backbone infrastructures & gigabit WAN connections.



Firebox T10

TECHNICAL SPECIFICATIONS

THROUGHPUT

Firewall throughput	200 Mbps
VPN throughput	30 Mbps
AV throughput	70 Mbps
IPS throughput	80 Mbps
UTM throughput	55 Mbps
Interfaces 10/100/1000	3 copper
I/O interfaces	1 SRL/1 USB
Concurrent connections (bi-directional)	7,500
New connections per second	1,000
VLANs	10
Authenticated users limit	200

VPN TUNNELS

Branch Office VPN	5
Mobile VPN IPSec	5
Mobile VPN SSL/L2TP	5

SECURITY FEATURES

Firewall	Stateful packet inspection, deep packet inspection, proxy firewall
Application proxies	HTTP, HTTPS, SMTP, FTP, DNS, TCP, POP3
Threat protection	DoS attacks, fragmented packets, blended threats and more
VoIP	H.323, SIP, call setup and session security
Filtering options	Browser Safe Search, YouTube for Schools
Security subscriptions	Application Control, IPS, WebBlocker, GAV, Data Loss Prevention, spamBlocker, Reputation Enabled Defense, APT Blocker

VPN & AUTHENTICATION

Encryption	DES, 3DES, AES 128-, 192-, 256-bit
IPSec	SHA-1, SHA-2, MD5, IKE pre-shared key, 3rd party cert
Single sign-on	Supports Windows, Mac OS X, mobile operating systems
Authentication	RADIUS, LDAP, Windows Active Directory, VASCO, RSA SecurID, internal database

MANAGEMENT

Logging and notifications	WatchGuard, Syslog, SNMP v2/v3
User interfaces	Centralized console (WSM), Web UI, scriptable CLI
Reporting	WatchGuard Dimension includes 70 pre-defined reports, executive summary and visibility tools

CERTIFICATIONS

Security	Pending: ICSA Firewall, ICSA IPSec VPN
Safety	NRTL/C, CB
Network	IPv6 Ready Gold (routing)
Hazardous substance control	WEEE, RoHS, REACH



STANDARD NETWORKING

QoS	8 priority queues, DiffServ, modified strict queuing
IP address assignment	Static, DHCP (server, client, relay), PPPoE, DynDNS
NAT	Static, dynamic, 1:1, IPSec traversal, policy-based
Other features	Static routing, port Independence, transparent/drop-in mode



PHYSICAL AND POWER SPECIFICATIONS

Product Dimensions	7.5" x 6.0" x 1.25" (19 x 15.2 x 3.2 cm)
Shipping Dimensions	12.5" x 7.25" x 2" (32 x 18.4 x 5 cm)
Shipping Weight	3.1 lbs (1.5 Kg)
AC Power	100-240 VAC Autosensing
Power Consumption	U.S. 15 Watts (51 BTU/hr) (max)
Rack Mountable	No

ENVIRONMENT	OPERATING	STORAGE
Temperature	32° F to 104° F 0° C to 40° C	-40° F to 158° F -40° C to 70° C
Relative Humidity	10% to 85% non-condensing	10% to 95% non-condensing
Altitude	0 to 9,843 ft at 95° F (3,000 m at 35° C)	0 to 15,000 ft at 95° F (4,570 m at 35° C)
MTBF	129,955 hours at 104° F (40° C)	

STRONG SECURITY AT EVERY LAYER

WatchGuard uses a best-of-breed strategy to create the most reliable security solutions on the market. By partnering with industry-leading technology vendors, WatchGuard delivers an all-star family of UTM network security products.

SOPHOS **websense** **commtouch**

AVG **TREND MICRO** **lastline**

EXPERT GUIDANCE AND SUPPORT

An initial subscription to LiveSecurity® Service is included with every Firebox T10 appliance. LiveSecurity provides hardware warranty with advance hardware replacement, technical support, and software updates.

MULTIPLE PURCHASE OPTIONS

The flexibility of WatchGuard's integrated UTM platform makes it easy to have exactly the security components your business network requires. Talk to your authorized WatchGuard reseller about very affordable bundled subscriptions for the Firebox T10.

Contact your WatchGuard reseller or call WatchGuard directly (1.800.734.9905) for help determining the right security solution for your network.

U.S. SALES 1.800.734.9905 INTERNATIONAL SALES +1.206.613.0895

www.watchguard.com

No express or implied warranties are provided for herein. All specifications are subject to change and expected future products, features or functionality will be provided on an if and when available basis. © 2014 WatchGuard Technologies, Inc. All rights reserved. WatchGuard, the WatchGuard logo, Firebox, Firewall, and LiveSecurity are registered trademarks of WatchGuard Technologies, Inc. in the United States and/or other countries. All other trademarks are the property of their respective owners. Part No. WGCE66830_040414