

568677

Hygiene Bucket, 12 Litre(s), Lime



This award-winning bucket is ideal for transporting cleaning chemicals and both hot and cold ingredients. It has a drip-free spout, a hand grip that is raised from the base, and a sturdy stainless steel handle. It is also calibrated for a variety of measuring units. The flat side prevents spillage and the bucket has its own wall bracket, 16200, for storage.

Technical Data

Item Number	568677
Volume	12 Litre(s)
Material	Polypropylene Stainless Steel (AISI 304)
Complies with (EC) 1935/2004 on food contact materials ¹	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Meets the REACH Regulation (EC) No. 1907/2006	Yes
Use of Phthalates	No
Is Halal compliant	Yes
Box Quantity	6 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	90 Pcs.
Quantity Per Layer (Pallet)	18 Pcs.
Box Length	740 mm
Box Width	340 mm
Box Height	320 mm
Length/Depth	325 mm
Width	330 mm
Height	330 mm
Gross Weight	1,09 kg
Net Weight	1 kg
Cubik metre	0,0354 M3
Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max. usage temperature (for food contact)	100 °C
Max usage temperature (non food contact)	100 °C
Min. usage temperature ³	-20 °C
Max. drying temperature	120 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	10,5 pH
GTIN-13 Number	5705022014282
GTIN-14 Number (Box quantity)	15705028014313
Commodity Code	39233090
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its

intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

1. See Declaration of Compliance for further details on food contact
3. Do not store the product below 0° Celsius.