

Professional SteelCore cable reel SC 2100 IP 44, 25 m H07RN-F 3G1.5

For construction site use in accordance with DGUV 203-006 (formerly BGI 608) and permanent outdoor use IP 44.



MADE IN GERMANY



Product number 9191250110
EAN 4007123687626

DESCRIPTION

- Reel body made of sheet steel, front and rear insulated for robust operation.
- Innovative „cablepilot“ carrying handle for perfect cable routing. Swings on both sides for easy carrying and hanging.
- Large, sturdy folding twist handle for effortless winding and unwinding of the cable.
- Reel body cold impact resistant down to -25 °C.
- Insensitive to petrol and oils.
- The RN cable is very robust, oil-resistant and particularly suitable for professional use.
- RN cable is approved for difficult building conditions in accordance with VDE 0100 Part 704.
- 4 splash-proof sockets with earthing contact, with self-closing lids.
- With extra robust safety plug.
- Overheating protection with indicator light in the event of overheating and overloading.
- With visual readiness indicator in the socket insert.
- Category 2 equipment (K2 DGUV 203-005): For use in harsh operating conditions with high mechanical, physical and chemical influences.

TECHNICAL DATA

Cable quality	Rubber-Neoprene	Plug system socket	Type F (Protective contact)
Cable length	25 m	Plug system plug	Type E and F (Protective contact with earth hole)
Cable designation	H07RN-F 3G1,5	Max. current carrying capacity	16 A
Cable colour	black	Nominal input voltage	230 V
Reel diameter	290 mm	Degree of protection (IP)	IP44
Plug system CEE socket	Without		

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1	Weight of product (including packaging)	6.73 kg
Weight of product (without packaging)	6.24 kg	Dimension LxWxH (incl. packing)	22 cm x 32 cm x 40 cm
Dimension LxWxH (without packing)	21 cm x 30.5 cm x 39 cm		

SCOPE OF DELIVERY

Professional SteelCore cable reel SC 2100 IP44

Hugo Brennenstuhl GmbH & Co. KG

www.brennenstuhl.com

All products are subject to technical changes.