

495A - HEAVY-DUTY END NIPPERS | 495A.22EL



Norm :

NF ISO 9242, ISO 9242, DIN ISO 9242

Description

- Rounded, semi-rigid handles designed to turn quickly in the hand.
- 60/62 HRC high-frequency hardened cutting edges for long life.
- Cutting capacity:
 - To diameter 4.5 mm on soft wire (300 mm model).
 - Max. on hard wire 160 kg/mm².
- Finish: burnished, polished head.

Information

B [mm]	31
C [mm]	10,5
E [mm]	13
H [mm]	23
L [mm]	220
[g]	310

