

FEATURES

- **10 m Length:** Provides ample reach for connecting devices at a distance.
- **IEC C13 to BS 1363/A Connectors:** Ensures compatibility with a wide range of devices and power outlets.
- **13 A Current Rating:** Supports high-power devices safely.
- **250 V Voltage Rating:** Suitable for standard electrical systems.
- **Black PVC Jacket:** Offers durability and protection against wear and tear.
- **Straight Mains Socket Type:** Facilitates easy and secure connections.

RS PRO 10m Power Cable, IEC C13 to BS 1363/A

RS Stock No: 558-964



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO power cable is designed for reliable electrical connections in various environments. With a length of 10 metres, it offers flexibility and convenience for connecting devices to power sources. The cable features an IEC C13 connector on one end and a BS 1363/A plug on the other, making it suitable for use in the UK and compatible regions. It supports a current rating of 13 A and a voltage of 250 V, ensuring efficient power delivery.

General Specifications

Connector Type A	IEC C13
Connector Type B	BS 1363/A
Jacket Colour	Black
Mains Socket Type	Straight
Product Type	Power Cable

Mechanical Specifications

Cable Length	10 m
Jacket Material	Polyvinyl Chloride

Electrical Specifications

Current Rating	13 A
Voltage	250 V

Approvals

Standards/Approvals	ASTA, CCCs, CSA, EAC, ENEC 11, ICC, JET, PSE, SII, RCM N10544, Singapore Safety Mark, UL
---------------------	--

