














## BP919



### RATCHET 1/4"

- Ratchet 1/4"
- Rubber grip
- Rubber boot included
- Balanced lightweight housing
- All ball bearing construction and high strength alloy steel gear system
- Hard coated motor plates














	 731415			<b>BAR</b>	 inch	 mm	 U/min	 Nm	 min-1	 dBA	 m/sec <sup>2</sup>	 mm	 kg
BP919	0184200	1	1/4"	6.2	1/4"	10	40	0-47	235	84	2.5	198	0.59

## BP700



### RATCHET 1/4"

- 1/4" Mini ratchet
- Composite housing
- Power regulator














	 731415			<b>BAR</b>	 inch	 mm	 U/min	 Nm	 min-1	 dBA	 m/sec <sup>2</sup>	 mm	 kg
BP700	0134458	1	1/4"	6.3	1/4"	10	65	0-30	300	94	3.60	133	0.50

## BP920



### RATCHET 3/8"

- Ratchet 3/8"
- Rubber grip
- Rubber boot included
- Balanced lightweight housing
- All ball bearing construction and high strength alloy steel gear system
- Hard coated motor plates

	 731415			<b>BAR</b>	 inch	 mm	 U/min	 Nm	 min-1	 dBA	 m/sec <sup>2</sup>	 mm	 kg
BP920	0184217	1	3/8"	6.2	1/4"	10	40	0-47	235	84	2.5	198	0.59