

## Label - EML (26,5X17,5)R SR CUS - 0824318

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Label, can be ordered: By line, silver/matt, labeled according to customer specifications, Mounting type: Adhesive, Lettering field: 26.5 x 17.5 mm



The figure shows the EML (15X9)R SR product variant

### Why buy this product

- ✓ All EML ... labels can also be supplied labeled according to customer requirements
- ✓ The EML ... materials are UL-listed



### Key commercial data

|                                      |                                                                                                         |
|--------------------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit                         | 1 pc                                                                                                    |
| GTIN                                 | <br>4 046356 351843 |
| Weight per Piece (excluding packing) | 1.99 g                                                                                                  |
| Custom tariff number                 | 39199000                                                                                                |
| Country of origin                    | Germany                                                                                                 |
| Note                                 | Made to Order (non-returnable)                                                                          |

### Technical data

#### Dimensions

|            |         |
|------------|---------|
| Length (b) | 26.5 mm |
| Width (a)  | 17.5 mm |

#### Ambient conditions

|                                 |                                |
|---------------------------------|--------------------------------|
| Ambient temperature (operation) | -40 °C ... 150 °C              |
| Ambient temperature (assembly)  | > 5 °C                         |
| Recommended storage conditions  | 22 °C / 50 % relative humidity |

#### General

|            |                                |
|------------|--------------------------------|
| Color      | silver/matt                    |
| Components | free from silicone and halogen |
| Material   | Polyester                      |

## Label - EML (26,5X17,5)R SR CUS - 0824318

### Technical data

#### General

|                                                                     |                                     |
|---------------------------------------------------------------------|-------------------------------------|
| Wipe resistance                                                     | DIN EN 61010-1 (VDE 0411-1)         |
| Number of individual labels per row                                 | 3                                   |
| RoHS compliant                                                      | Yes                                 |
| Adhesive                                                            | Acrylic                             |
| File number                                                         | UL-MH48542 / PC-018                 |
| Printability                                                        | Thermal transfer                    |
| Device                                                              | 5146477 THERMOMARK ROLL             |
|                                                                     | 5146723 THERMOMARK ROLL X1          |
|                                                                     | 5146231 THERMOMARK X1.2             |
|                                                                     | 5146257 THERMOMARK S1.1             |
| Ink ribbon                                                          | 5145384 THERMOMARK-RIBBON 110       |
| Test for substances that would hinder coating with paint or varnish | VW PV 3.10.7:2005-02                |
| Result                                                              | Test passed                         |
| Test specification weathering-resistance                            | Following ISO 4892-2:2013-03        |
| Test duration                                                       | 96 h                                |
| Wipe resistance test result                                         | Test passed                         |
| Salt spray test specification                                       | DIN EN ISO 9227:2012-09             |
| Test duration                                                       | 96 h                                |
| Salt spray testing result                                           | Test passed                         |
| Alternating condensation climate with SO2 test specification        | DIN 50018:2013-05                   |
| Climate level                                                       | AHT 1.0 S                           |
| Cycles                                                              | 2                                   |
| Condensation test result                                            | Test passed                         |
| Wipe resistance of test specification inscriptions                  | DIN EN 61010-1 (VDE 0411-1):2011-07 |
| Result                                                              | Test passed                         |
| Foil strength                                                       | 50 µm                               |
| Adhesive strength                                                   | 24 µm                               |
| Marking mounting type                                               | Adhesive                            |

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 24190219 |
| eCl@ss 4.1 | 24190219 |
| eCl@ss 5.0 | 27149103 |
| eCl@ss 5.1 | 27141137 |
| eCl@ss 6.0 | 27141137 |
| eCl@ss 7.0 | 27141137 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000761 |
|----------|----------|

## Label - EML (26,5X17,5)R SR CUS - 0824318

### Classifications

#### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC000761 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121410 |
| UNSPSC 12.01  | 39121410 |
| UNSPSC 13.2   | 39121410 |

### Approvals

#### Approvals

Approvals

UL Recognized

Ex Approvals

Approvals submitted

#### Approval details

UL Recognized 

### Accessories

#### Accessories

##### Marker carriers

Marker carriers - CARRIER-EMP 22 (27X18) - 0827448



Marker carriers, black, unlabeled, Mounting type: Screws, rivets, Diameter: 22 mm, Lettering field: 27 x 18 mm

## Label - EML (26,5X17,5)R SR CUS - 0824318

### Accessories

Marker carriers - CARRIER-EMLP 22 (27X18) - 0828987



Marker carriers, black, unlabeled, Mounting type: Screws, rivets, Diameter: 22 mm, Lettering field: 27 x 18 mm