

## Datasheet

# RS Pro Grey 2 Gang PC Switched Power Socket, Type G - British, 13A, Surface Mount, IP66

RS Stock No: **699-7092**



## Product Details

RS Pro 2-gang switched power socket has polycarbonate construction. This type G - British socket is suitable for applications with a current requirement of up to 13 A. It includes colour-coded terminals, removable blanking caps and see-through cover for usage flexibility. The surface mountable device protects the potentially dangerous electricity supply in the most arduous conditions.

## Features and Benefits

- Designed to protect the potentially dangerous electricity supply in the most arduous of conditions
- Colour coded terminals with backed out captive screws
- Covers to seal the fixing screws
- Earth terminal in mounting box
- All cable entries in the 4 sides have removable blanking caps
- Cover will stay open to allow for easy access to sockets
- See through cover allows status of switches to be seen

**Specifications:**

Colour Family	Grey
Colour	Grey
Current Rating	13 A
Earth Terminal	Yes
Faceplate Mounting Type	Screw Covers Supplied
Finish	Fine Textured
Fixing Standard	BS
International Protection Rating	IP66
Material	PC
Minimum Box Depth	80 mm
Mounting Style	Surface Mount
Number of Gangs	2
Number of Poles	2
Overall Depth	80 mm
Overall Dimensions	171 x 154 x 80 mm
Overall Height	160 mm
Overall Width	200 mm
Socket Type	Type G - British
Special Features	LED Illumination
Switch Style	Rocker
Switched	Yes
Terminal Type	Captive Screw
Voltage Rating	230 V ac