



brennenstuhl®

Alu-Office-Line 60.000 A surge protection extension lead with USB charging function 4-way 1.8 m H05VV-F 3G1.5

Extension lead in a slim design as an optimal power supply in the home office or at the workplace.



MADE IN GERMANY



Product number 1391020410
EAN 4007123677047

DESCRIPTION

- Protection for your devices against interference in the power grid, such as overvoltages, indirect lightning strikes or line noise, with a maximum sum of leakage currents of up to 60,000 A.
- Elegant, slim design in desktop version made of aluminium with robust, matt anodised surface.
- Convenient for plugging in and switching devices directly on the desk.
- Sockets with earthing contact in 45° arrangement, also for angled plugs.
- Illuminated safety switch, can be switched on/off with two poles.
- Sockets with increased touch protection.
- Charging of your connected devices thanks to two integrated USB A ports 5 V/3.10 A, 15.5 W.
- Recommended accessories: table clamps with locking screws (1990500010).

TECHNICAL DATA

Cable quality	PVC	Max. current carrying capacity	16 A
Cable length	1.8 m	USB charging units	2x /Technische Attribute/Anschlussbuchse/Typ A
Cable designation	H05VV-F 3G1,5	Max. output current USB	3.1 A
Plug system plug	Type E and F (Protective contact with earth hole)	Output socket type A	2
Socket outlets total	4	With surge protection	Yes
Socket outlets switchable	1x 4	With interference suppressor filter	No
Circuit breaker	No	Colour	silver/black

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1	Weight of product (including packaging)	1.13 kg
Weight of product (without packaging)	0.96 kg	Dimension LxWxH (incl. packing)	10.5 cm x 11.5 cm x 59 cm
Dimension LxWxH (without packing)	10.5 cm x 10.5 cm x 48 cm		

SCOPE OF DELIVERY

Alu-Office-Line surge protection extension lead